








RECOMMENDED P. C. B. LAYOUT

	8	LOCK SCREW	STEEL	2	NICKEL PLATING	M2×0.4
	7	HEX. NUT	BRASS	2	NICKEL PLATING	M2×0.4
	6	EARTH PLATE	PHOSPHOR BRONZE	2	NICKEL PLATING	————
	5	SQR. NUT	BRASS	2	NICKEL PLATING	M2×0.4
	4	INSULATOR B	PPS (GF)	1	————	UL94V-0 BLACK COLOR
	3	CONTACT	PHOSPHOR BRONZE	26	SEE NOTE #2	————
	2	SHELL	STEEL	1	NICKEL PLATING	————
	1	INSULATOR A	LCP (GF)	1	————	UL94V-0 BLACK COLOR

				3	CONTACT	PHOSPHOR BRONZE	26	SEE NOTE #2	BLACK COLOR	
				2	SHELL	STEEL	1	NICKEL PLATING		
	APP. 11 2005	Y. K	Add P/N	1	INSULATOR A	LCP (GF)	1		UL94V-0 BLACK COLOR	
LTR.	DATE	BY	REV.	DESCRIPT	No.	PART NAME	MATERIAL	QTY	FINISH	NOTE
DATE May. 18. 2004		SCALE 2 / 1		UNIT mm (INCH)	3RD. A. P		HONDA TSUSHIN KOGYO CO., LTD.			
APP. DATE&REV.										
DR.		DE.		CHK.	CHK.	APP.	NAME 0.8mm SPACING 26POS. RIGHTANGLE FEMALE CONNECTOR			
Y. KATO		Y. KATO		—	C. NUNOKAWA	H. EBIHARA	PART NO.		HDR-EA26LFYPG1-() +	REV. 1 A