



KLU225, Copper Terminal, Offset Tongue, 1 Hole, 2-4/0 AWG (Str), 5/16" Stud, 1 Screw

By Burndy
Catalog # [KLU225](#)



Copper Terminal, Offset Tongue, 1 Hole, 2-4/0 AWG (Str), 5/16" Stud, 1 Screw.

Features

- Range-taking design reduces SKUs required in inventory
- High conductivity copper alloy for long lasting reliable contact
- Compact design, easy to install
- Slot Robertson screw, hex head, hex socket bolt require no special installation tools

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar

General

Catalog Number	KLU225
EU RoHS Indicator	Yes
Hardware Type	7/16 UNF Socket/HexScrew
Installation Torque	120
Recommended in-lb	
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Sub Brand	SCRULUG
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810351413
UPC 14 Digit GTIN	00781810351413

Dimensions

Dimension - B Length fraction	15/16 in
Dimension - Bolt Size fraction	5/16
Dimension - Height mm	0 mm

Dimension - Hole Size inch	0.34 in
Dimension - Hole Size mm	9 mm
Dimension - N inch	0.51 in
Dimension - Pad Width inch	0.99 in
Dimension - Screw Size inch	7/16
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size inch	5/16

Conductor Related

Conductor - Copper Str Size Range	2 AWG-4/0 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	120
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_KLU_LineArt](#)
[Sales Drawings - sd207469-01](#)
[Specifications - KLU225](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-KLU225-SPEC-EN | REV 7/2025