

MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929**SWITCH - BASIC**CATALOG LISTING
BA-2R164-A4**BA-2R164-A4**
PAGE 1 OF 1**M**DRAWING
NUMBER

4

ISSUE

REPLACES

RELEASE NO. PR-5616

CHECK

REVISIONS

A	CO-73287-G	20 OCT 93
B	CO-77588	K D R 29 MAR 94
C	C093346	DLT 23 SEP 98

CHECK

17 FEB 76

CEB

76


FEB 76

J A L 13

FORMTEK

FO-52848-A


DRAWN

**NOTE**

 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE ----- 14 - 22 OZ
RELEASE FORCE ----- 10 OZ MIN
DIFFERENTIAL TRAVEL ----- .005 - .007
OVERTRAVEL ----- .010 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

UL LISTED - FILE E12252
CODE L145 20A-125, 250, 480VAC
1HP-125VAC; 2HP-250VAC
10A-125VAC "L"; 2A-600VAC
1/2A-125VDC; 1/4A-250VDC

L288
L299
L308



20(3)A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE $\pm$

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/16	X
ONE PLACE	X.X	0.015	X.X
TWO PLACES	X.XX	0.0015	X.XX
THREE PLACES	X.XXX	0.00015	X.XXX

DESIGN UNITS ☐ SI METRICUS CUSTOMARY ☒

WEIGHT .063 LB