


HONEYWELL PART NUMBER
11SM401-H2
PRODUCT CODE TWY0120

REV	DOCUMENT	CHANGED BY	CHECK
6	0038104	PK 23APR08	ASD



B

A

A



PLASTIC PLUNGER



NOTE -
1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ±.002 CENTERS
2 - TERMINALS ARE PLATED FOR SOLDERING
3 - DEAD BREAK CONDITIONS:
A - MAX AMOUNT PERMISSIBLE - - - - - .0002 IN.

RELEASE NO.	SR - 12207
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 			DRAWN	VK	27 NOV 07		Honeywell			
OPERATING FORCE — — — 31/2 OZ MAX		CONTACT ARRANGEMENT SPDT						CHECK	RJ	27 NOV 07					
RELEASE FORCE— — — — 1 OZ MIN		30 VOLTS DC RATING			0.030 0.015 0.005			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH - BASIC			
DIFFERENTIAL TRAVEL— — — .001 MAX			SEA LEVEL	50,000 FT											
OVERTRAVEL — — — — — .005 MIN		INDUCTIVE	3 AMP	2.5 AMP											
		RESISTIVE	5 AMP	5 AMP											
		MAXIMUM INRUSH 24 AMP					INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE	TYPE	DRAWING NAME		REV
		APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4  		UL, CSA					5A, 250 VAC  		BRAND	L4	B
							RASTER				SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1	