

**Part Number :** [386608803](#)

**Product Description :** 12.70mm Pitch Beau PCB Tri-Barrier Terminal Strip, without Mounting Ends, 600V, 3 Circuits

**Series Number :** 38660

**Status :** Obsolete

**Product Category :** Terminal Blocks and Barrier Strip

**Engineering Part Number :** 66503-RC




---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Obsolete
Category	Terminal Blocks and Barrier Strip
Series	38660
Description	12.70mm Pitch Beau PCB Tri-Barrier Terminal Strip, without Mounting Ends, 600V, 3 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Name	Fixed Mount Barrier
Type	Barrier Strips
UPC	883906403058

### Electrical

Current - Maximum per Contact	45.0A
Voltage - Maximum	600V

### Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polysulfone
Net Weight	29.030/g
Number of Rows	1
Orientation	Vertical
Panel Mount	No

PCB Retention	Yes
PC Tail Length	4.06mm
Pitch - Mating Interface	N/A
Pitch - Termination Interface	12.70mm
Polarized to Mating Part	N/A
Shrouded	Tri-Barrier
Stackable	No
Temperature Range - Operating	-40° to +110°C
Wire Size (AWG)	10, 12, 14, 16, 18, 8
Wire Size mm <sup>2</sup>	0.82-8.37

---

This document was generated on Apr 11, 2026

Obsolete