

Part Number : [1200895011](#)

Product Description : Y Nano-Change (M8) Splitter to Nano-Change (M8) 3 Pole Female to 3 Pole Male

Series Number : 120089

Status : Active

Product Category : Industrial Tees and Splitters

Engineering Part Number : 0808 03LMF 00000




Documents and Resources

Drawings

[1200895011_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120089
Description	Y Nano-Change (M8) Splitter to Nano-Change (M8) 3 Pole Female to 3 Pole Male
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Splitter - Solid Body
UPC	883906783952

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Drop Connector	Nano-Change (M8)
Drop Gender	Male
Keyway	None
Left Trunk Connector	Nano-Change (M8)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Net Weight	1.000/g

Poles	4
Right Trunk Connector	Nano-Change (M8)
Right Trunk Gender	Female
Temperature Range - Operating	-20° to +90°C

This document was generated on May 19, 2026