

# BGA Heat Sink - High Performance ASIC Cooling



|                         |                                                                        |
|-------------------------|------------------------------------------------------------------------|
| ATS Part#:              | ATS-56006-C1-R0                                                        |
| Description:            | 50.00 x 45.00 x 12.00 mm BGA Heat Sink - High Performance ASIC Cooling |
| Heat Sink Type:         | ASIC Cooling                                                           |
| Heat Sink Attachment:   | Thermal Tape                                                           |
| Equivalent Part Number: | ATS-56006-C3-R0                                                        |

\*Image above is for illustration purpose only.


## Features & Benefits

- **maxiFLOW™** design features a low profile, spread fin array that maximizes surface area for more effective convection (air) cooling
- Designed specifically for ASIC package and their unique cooling requirements
- Comes preassembled with high performance thermal interface material

## Thermal Performance

| AIR VELOCITY       |               | @200 LFM<br>1.0 M/S | @300 LFM<br>1.5 M/S | @400 LFM<br>2.0 M/S | @500 LFM<br>2.5 M/S | @600 LFM<br>3.0 M/S | @700 LFM<br>3.5 M/S | @800 LFM<br>4.0 M/S |
|--------------------|---------------|---------------------|---------------------|---------------------|---------------------|---------------------|---------------------|---------------------|
| THERMAL RESISTANCE | Unducted Flow | 3.9 °C/W            | 3.1 °C/W            | 2.3 °C/W            | 2 °C/W              | 1.7 °C/W            | 1.5 °C/W            | 1.4 °C/W            |
|                    | Ducted Flow   | 1.7                 | N/A                 | N/A                 | N/A                 | N/A                 | N/A                 | N/A                 |

## Product Detail

| Schematic Image                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | Dimension A | Dimension B | Dimension C | Dimension D | TIM  | Finish         |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|-------------|-------------|-------------|------|----------------|
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   | 50.00 mm    | 45.00 mm    | 12.00 mm    | 59.2 mm     | T412 | BLACK-ANODIZED |
| <p><b>Notes:</b></p> <ul style="list-style-type: none"><li>• Dimension <b>A</b> and <b>B</b> refer to component size.</li><li>• Dimension <b>C</b> is the heat sink height from the bottom of the base to the top of the fin field.</li><li>• ATS-56006-C3-R0 is the exact heat sink assembly with an equivalent thermal interface material (Saint-Gobain C675).</li><li>• Thermal performance data are provided for reference only. Actual performance may vary by application.</li><li>• ATS reserves the right to update or change its products without notice to improve the design or performance.</li><li>• ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant.</li><li>• Contact ATS to learn about custom options available.</li></ul> |             |             |             |             |      |                |

\*Image above is for illustration purpose only.

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), [sales@qats.com](mailto:sales@qats.com) or [www.qats.com](http://www.qats.com).

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA

