




PRODUCT NUMBER: 0365-0-15-01-23-01-10-0

www.mill-max.com
DATA SHEET



0365-0-15-01-23-01-10-0 SPECIFICATIONS

| General Info | |
|--|--|
| Description ¹ : Receptacle With No Tail | |
| Mounting Feature ² : | Press-Fit into a Plated Through Hole (PTH) |
| Mounting Hole: | .106" (2,692mm) |
| Pin Diameter Range: | .045"-.065" (1,143-1,651mm) |
| Packaging: | Packaged in Bulk |
| RoHS: | No |
| Product Lifecycle ³ : | Active |
| Country Of Origin: | USA |

| Materials | |
|--------------------------------|--|
| Shell Material ⁴ : | Brass Alloy |
| Shell Plating ⁵ : | 200 - 300 μ " Tin/Lead over Nickel |
| Contact Plating ⁶ : | 200 - 300 μ " Tin/Lead over Nickel |


| Technical Specs | |
|--|---|
| Mechanical life | 1,000 Cycles Minimum (Durability) ⁷ : |
| Operating Temperature Range ⁸ : | -55/+125° C |
| Maximum Current: | 18A @ 30° C Temp. Rise |
| Maximum Derated Current: | 14.4A |
| Contact Resistance: | 10 m Ω Max |
| Shock ⁹ : | No Elect. Discontinuity > 1 μ s @ 50g |
| Vibration ¹⁰ : | No Elect. Discontinuity > 1 μ s @ 10-2000HZ, 20 G |

NOTES:

1. Standard Tolerances:
Lengths $\pm .005$ " (0,13)
Diameters: $\pm .002$ " (0,051)
Angles: $\pm 2^\circ$
2. The suggested mounting hole represents the plated through-hole size. Press-fit pins designed for plated through-holes require the bare board drill size to be .001" (.0254 mm) larger than the diameter of the press-fit feature. This is a general guideline; your application may require different specifications
3. Part is Active and in Production, No Scheduled Obsolescence
4. Brass Alloy 360 per ASTM B 16, or 385 per ASTM B455
5. TIN/LEAD (93/7) per ASTM B 545 (Appendix X6.3.2.5 to eliminate whisker growth) Bright finish; NICKEL per ASTM B 689, Type 2 (Bright)
6. TIN/LEAD (93/7) per ASTM B 545 (Appendix X6.3.2.5 to eliminate whisker growth) Bright finish, NICKEL per ASTM B 689, Type 2 (Bright)
7. Receptacles are capable of 1,000 Minimum insertion/extraction cycles for a broad range of applications. Mating pin size, shape and finish, along with application specific variables, will affect the life of a receptacle contact.
8. Per IEC 60512-11-(4,-9,-10,-12)
9. Per IEC 60512-6-3: Test 6c: Shock
10. Per IEC 60512-6-4: Test 6d: Vibration (sinusoidal)

ADDITIONAL PARTS, PACKAGING, & ASSEMBLY INFO



0365-0-57 Tape & Reel Details



CONTACT:

#23 CONTACT

FOR .045"-.065" DIAMETER PINS ($\delta = .008$)
6-FINGER (BeCu), GROUP G



The insertion / extraction force characteristics above were derived using a 30 microinch gold-plated contact and polished steel gauge pins having a bullet-shaped tip. The curves represent typical average values; they are best used to compare the differences between similar size contacts and to guide you in selecting one that is suitable for your application. Your results may vary, so for your specification, we encourage you to obtain complimentary samples for your evaluation.

| | | | |
|------------------------------|------------------------|--------------------------------------|-----------------|
| Material | Beryllium Copper | Fingers | 6 |
| Compliance (δ) | 0.008 | Length | .100" (2,540mm) |
| Maximum Current | 18A @ 30° C Temp. Rise | Maximum Operating Temp @ Max Current | 120.00° C |
| 20% De-rated Maximum Current | 14.40A | Contact Resistance | 10.00mΩ Max |
| Contact Group | G | | |

ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance , Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

RELATED LINKS AND DOCUMENTS

Application Note: (<https://www.mill-max.com/sites/default/files/external/assets/2018-01/Press-fit%20PCB%20Pins%20for%20Plated%20Thru-Holes.pdf>)

Environmental Compliance: (<https://www.mill-max.com/rohs>)