
APT50M50JFLL

500V 71A 0.050Ω


POWER MOS 7® FREDFET



ISOTOP®

Power MOS 7® is a new generation of low loss, high voltage, N-Channel enhancement mode power MOSFETS. Both conduction and switching losses are addressed with Power MOS 7® by significantly lowering $R_{DS(ON)}$ and Q_g. Power MOS 7® combines lower conduction and switching losses along with exceptionally fast switching speeds inherent with APT's patented metal gate structure.

- **Lower Input Capacitance**
- **Lower Miller Capacitance**
- **Lower Gate Charge, Qg**
- **Increased Power Dissipation**
- **Easier To Drive**
- **Popular SOT-227 Package**
- **FAST RECOVERY BODY DIODE**



MAXIMUM RATINGS All Ratings: T_C = 25°C unless otherwise specified.

Symbol	Parameter	APT50M50JLL	UNIT
V_{DSS}	Drain-Source Voltage	500	Volts
I_D	Continuous Drain Current @ T_C = 25°C	71	Amps
I_{DM}	Pulsed Drain Current ①	284	
V_{GS}	Gate-Source Voltage Continuous	±30	Volts
V_{GSM}	Gate-Source Voltage Transient	±40	
P_D	Total Power Dissipation @ T_C = 25°C	595	Watts
	Linear Derating Factor	4.76	W/°C
T_J,T_{STG}	Operating and Storage Junction Temperature Range	-55 to 150	°C
T_L	Lead Temperature: 0.063" from Case for 10 Sec.	300	
I_{AR}	Avalanche Current ① (Repetitive and Non-Repetitive)	71	Amps
E_{AR}	Repetitive Avalanche Energy ①	50	mJ
E_{AS}	Single Pulse Avalanche Energy ④	3200	

STATIC ELECTRICAL CHARACTERISTICS

Symbol	Characteristic / Test Conditions	MIN	TYP	MAX	UNIT
BV_{DSS}	Drain-Source Breakdown Voltage (V_{GS} = 0V, I_D = 250μA)	500			Volts
$R_{DS(on)}$	Drain-Source On-State Resistance ② (V_{GS} = 10V, 35.5A)			0.050	Ohms
I_{DSS}	Zero Gate Voltage Drain Current (V_{DS} = 500V, V_{GS} = 0V)			100	μA
	Zero Gate Voltage Drain Current (V_{DS} = 400V, V_{GS} = 0V, T_C = 125°C)			500	
I_{GSS}	Gate-Source Leakage Current (V_{GS} = ±30V, V_{DS} = 0V)			±100	nA
$V_{GS(th)}$	Gate Threshold Voltage (V_{DS} = V_{GS}, I_D = 5mA)	3		5	Volts

CAUTION: These Devices are Sensitive to Electrostatic Discharge. Proper Handling Procedures Should Be Followed.

APT Website - http://www.advancedpower.com

050-7117 Rev B 3-2004

Downloaded from Arrow.com.

DYNAMIC CHARACTERISTICS

APT50M50JFLL

Symbol	Characteristic	Test Conditions	MIN	TYP	MAX	UNIT
C_{iss}	Input Capacitance	V_{GS} = 0V V_{DS} = 25V f = 1 MHz		10550		pF
C_{oss}	Output Capacitance			2060		
C_{rss}	Reverse Transfer Capacitance			105		
Q_g	Total Gate Charge ③	V_{GS} = 10V V_{DD} = 250V I_D = 71A @ 25°C		200		nC
Q_{gs}	Gate-Source Charge			50		
Q_{gd}	Gate-Drain ("Miller") Charge			105		
$t_{d(on)}$	Turn-on Delay Time	**RESISTIVE SWITCHING** V_{GS} = 15V V_{DD} = 250V I_D = 71A @ 25°C R_G = 0.6Ω		24		ns
t_r	Rise Time			18		
$t_{d(off)}$	Turn-off Delay Time			55		
t_f	Fall Time			10		
E_{on}	Turn-on Switching Energy ⑥	**INDUCTIVE SWITCHING @ 25°C** V_{DD} = 333V, V_{GS} = 15V I_D = 71A, R_G = 3Ω		1000		µJ
E_{off}	Turn-off Switching Energy			1040		
E_{on}	Turn-on Switching Energy ⑥	**INDUCTIVE SWITCHING @ 125°C** V_{DD} = 333V V_{GS} = 15V I_D = 71A, R_G = 3Ω		1580		
E_{off}	Turn-off Switching Energy			1160		

SOURCE-DRAIN DIODE RATINGS AND CHARACTERISTICS

Symbol	Characteristic / Test Conditions		MIN	TYP	MAX	UNIT
I_S	Continuous Source Current (Body Diode)				71	Amps
I_{SM}	Pulsed Source Current ① (Body Diode)				284	
V_{SD}	Diode Forward Voltage ② (V_{GS} = 0V, I_S = -71A)				1.3	Volts
dv/dt	Peak Diode Recovery dv/dt ⑤				15	V/ns
t_{rr}	Reverse Recovery Time (I_S = -71A, di/dt = 100A/µs)	T_j = 25°C			300	ns
		T_j = 125°C			600	
Q_{rr}	Reverse Recovery Charge (I_S = -71A, di/dt = 100A/µs)	T_j = 25°C		2.6		µC
		T_j = 125°C		10		
I_{RRM}	Peak Recovery Current (I_S = -71A, di/dt = 100A/µs)	T_j = 25°C		17		Amps
		T_j = 125°C		34		

THERMAL CHARACTERISTICS

Symbol	Characteristic	MIN	TYP	MAX	UNIT
$R_{\theta JC}$	Junction to Case			0.21	°C/W
$R_{\theta JA}$	Junction to Ambient			40	

① Repetitive Rating: Pulse width limited by maximum junction temperature

② Pulse Test: Pulse width < 380 µs, Duty Cycle < 2%

③ See MIL-STD-750 Method 3471

④ Starting T_j = +25°C, L = 1.27mH, R_G = 25Ω, Peak I_L = 71A

⑤ dv/dt numbers reflect the limitations of the test circuit rather than the device itself. $I_S \le$ -71A $di/dt \le$ 700A/µs $V_R \le$ 500V $T_J \le$ 150°C

⑥ Eon includes diode reverse recovery. See figures 18, 20.

APT Reserves the right to change, without notice, the specifications and information contained herein.




FIGURE 1, MAXIMUM EFFECTIVE TRANSIENT THERMAL IMPEDANCE, JUNCTION-TO-CASE vs PULSE DURATION

Downloaded from Arrow.com.




FIGURE 2, TRANSIENT THERMAL IMPEDANCE MODEL




FIGURE 3, LOW VOLTAGE OUTPUT CHARACTERISTICS




FIGURE 4, TRANSFER CHARACTERISTICS




FIGURE 5, $R_{DS(ON)}$ vs DRAIN CURRENT




FIGURE 6, MAXIMUM DRAIN CURRENT vs CASE TEMPERATURE




FIGURE 7, BREAKDOWN VOLTAGE vs TEMPERATURE




FIGURE 8, $R_{DS(ON)}$ vs. TEMPERATURE




FIGURE 9, THRESHOLD VOLTAGE vs TEMPERATURE

Downloaded from Arrow.com.




FIGURE 10, MAXIMUM SAFE OPERATING AREA




FIGURE 11, CAPACITANCE vs DRAIN-TO-SOURCE VOLTAGE




FIGURE 12, GATE CHARGE vs GATE-TO-SOURCE VOLTAGE




FIGURE 13, SOURCE-DRAIN DIODE FORWARD VOLTAGE




FIGURE 14, DELAY TIMES vs CURRENT




FIGURE 15, RISE AND FALL TIMES vs CURRENT




FIGURE 16, SWITCHING ENERGY vs CURRENT




FIGURE 17, SWITCHING ENERGY VS. GATE RESISTANCE

Downloaded from Arrow.com.




Figure 18, Turn-on Switching Waveforms and Definitions




Figure 19, Turn-off Switching Waveforms and Definitions





Figure 20, Inductive Switching Test Circuit

SOT-227 (ISOTOP®) Package Outline



Dimensions in Millimeters and (Inches)

ISOTOP® is a Registered Trademark of SGS Thomson. APT's products are covered by one or more of U.S.patents 4,895,810 5,045,903 5,089,434 5,182,234 5,019,522 5,262,336 6,503,786 5,256,583 4,748,103 5,283,202 5,231,474 5,434,095 5,528,058 and foreign patents. US and Foreign patents pending. All Rights Reserved.

Downloaded from Arrow.com.