

MLCC with Dipped Radial Lead

FA23C0G2W104JNU06

Applications

Automotive Grade

Feature

Mid

Mid Voltage (100 to 630V)

Halogen-free

Halogen-free

AEC-Q200


AEC-Q200

Series

FA

Status

Production



Images are for reference only and show exemplary products.

Size	
Length(L)	8.50mm Max.
Width(W)	11.00mm Max.
Thickness(T)	5.50mm Max.
Lead Gap(F)	5.00mm +0.80,-0.20mm
Lead Diameter(d)	0.50mm +0.10,-0.03mm

Electrical Characteristics	
Capacitance	100nF ±5%
Rated Voltage	450VDC
Withstanding Voltage	675VDC
Temperature Characteristic	C0G(0±30ppm/°C)
Q (Min.)	1000
Insulation Resistance (Min.)	5000MΩ

Other	
Soldering Method	Wave (Flow) Iron Soldering
Lead Length / Package Type	Taping
AEC-Q200	Yes
Package Quantity	1000pcs

Characteristic Graph

(This is reference data, and does not guarantee the products characteristics.)

?

RoHS

REACH SVHC-Free

Halogen Free

Lead Free

PDF file of this page

Contact

Documents

Catalog

Specification


RoHS Certificate

SVHC/REACH Certificate

Update

[Solution Guide] PCB Deflection Countermeasure / Acoustic Noise Countermeasure / Noise Countermeasures in Automotive DC Motors

Characterization Sheet



FA23C0G2W104JNU06

Change settings

DC Bias Characteristic

FA23C0G2W104JNU06

Change settings

FA23C0G2W104JNU06

Change settings

Temperature Characteristic

FA23C0G2W104JNU06(No Bias)
FA23C0G2W104JNU06(DC Bias = 450)

Change settings



- Selection Guides
- Search by Part No.
- Search by Characteristics
- Distributor Inventory Check
- Cross Reference

Products

- Capacitors >
- Inductors (Coils) >
- EMC Components >
- RF Components and Modules >
- Voltage / Current / Temperature Protection Devices >
- Sensors and Sensor Systems >
- Ceramic Switching / Heating, Piezo Components, Buzzers and Microphones >
- Transformers >
- Ferrites and Accessories >
- Noise Suppressing / Magnetic Sheet >
- Anechoic Chambers and Radio Wave Absorbers >
- Power Supplies >
- Magnets >
- Flash Storages >
- Wireless Power Transfer >
- FA Systems >
- Transparent Conductive Film >
- Micro Modules (Substrates with Built-in ICs, Products Utilizing with SESUB) >
- Solar Cells >
- Biosensor >
- Application Specific IC (ASIC) Development and Supply >

[Application Guides](#)

[Technical Support](#)

[Tech Library](#)

[Environment](#)

[Contact](#)

[News](#)

[Home](#)

[About TDK](#)

[TDK Worldwide](#)

[Terms of Use](#)

[Privacy Policy](#)

[Cookie Policy](#)

[Counterfeit Products](#)

Copyright(c) 2019 TDK Corporation. All rights reserved.
TDK logo is a trademark or registered trademark of TDK Corporation.

