



**NOTES:**

1. METALSHELLS.STELL; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. THREADED INSERTS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
4. COLLARS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
5. CONNECTOR WILL BE SUPPLIED WITHOUT CONTACTS
6. MAXIMUM TORQUE VALUE FOR THREAD: 6in.LB
7. CONNECTOR IS PART MARKED: DSS1XSXXG03X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance		scale: 2:1 (5:1)
				dim. in mm		material: SEE NOTES
				date	name	title: <b>D-SUB FEMALE</b> CRIMP STYLE 9pos. with threaded insert
				drawn 27.06.12	Henneboel	
				appd. 27.06.12	Koch	
				norm		
			d-old		dwg no:	
	a	Original			<b>16K1A3082</b>	DIN-A3 sh: 1
	rev.	description	date	name	<b>CONEC</b>	part no: <b>DSS1XSXXG03X</b>