

## SmartRack 12U Heavy-Duty Flat-Pack Low-Profile Switch-Depth Wall-Mount 2-Post Open Frame Rack

MODEL NUMBER: **SRWO12UHD**



Open frame rack stores 12U of 19-inch rack equipment up to 18 inches deep in network closets and other locations with limited floor space where a locked enclosure is not required. Allows easy access to equipment and cabling.

### Description

The SRWO12UHD SmartRack 12U Heavy-Duty Flat-Pack Low-Profile Switch-Depth Wall-Mount 2-Post Open Frame Rack stores and organizes EIA-standard 19-inch rack equipment compatible with 2-post mounting in network wiring closets, back offices and other secure areas with limited floor space where a locked enclosure is not required. Constructed from heavy-duty steel with a durable black powder-coated finish, the rack has a maximum load capacity of 200 lbs (90.7 kgs).

The open frame design allows unrestricted access for installing, configuring and servicing equipment and cabling. The rack is simple to assemble and mount to the wall. Threaded 12-24 mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails accommodate equipment up to 18 inches deep, such as network switches and patch panels. Assembly and equipment-mounting hardware is included.

### Features

#### Saves Valuable Workspace

- Perfect for network wiring closets, back offices and other secure areas with limited floor space where a locked enclosure is not required
- Stores and organizes EIA-standard 19 in. rack equipment compatible with 2-post mounting in 12U of space
- Maximum load capacity of 200 lbs (90.7 kgs)

#### 2-Post Open Frame Design

- Allows easy access for installing, configuring and servicing equipment and cabling

#### Easy Assembly and Installation

- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Vertical mounting rails accommodate equipment up to 18 in. deep, such as network switches and patch panels
- Rails support threaded-hole equipment mounting

### Highlights

- Maximum load capacity of 200 lbs (90.7 kgs)
- Allows easy access to equipment and cabling
- Stores 12U of 19 in. rack equipment up to 18 in. deep
- Simple to assemble and mount
- Assembly and equipment-mounting hardware included

### Package Includes

- (24) 12-24 equipment mounting screws
- (8) M5 button-head cap screws
- (8) M6 x 12 Phillips-head screws
- (2) Support straps
- (2) Vertical mounting rails
- (2) Top/bottom panel frames
- 3 mm hex key
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

- Rack spaces numbered for easy reference
- Includes assembly and equipment-mounting hardware

## Specifications

| OVERVIEW                            |                             |
|-------------------------------------|-----------------------------|
| UPC Code                            | 037332182654                |
| Device Compatibility                | Patch Panel; Network Switch |
| Rack Type                           | Open-Frame                  |
| PHYSICAL                            |                             |
| Color                               | Black                       |
| Rack Height                         | 12U                         |
| Rack Depth                          | Shallow                     |
| Maximum Device Depth (cm)           | 45.72                       |
| Maximum Device Depth (in.)          | 18                          |
| Maximum Device Depth (mm)           | 457                         |
| Shipping Dimensions (hwd / in.)     | 4.10 x 22.80 x 21.30        |
| Shipping Dimensions (hwd / cm)      | 10.41 x 57.91 x 54.10       |
| Shipping Weight (lbs.)              | 15.10                       |
| Shipping Weight (kg)                | 6.85                        |
| Unit Dimensions (hwd / in.)         | 24.800 x 20.110 x 18.240    |
| Unit Dimensions (hwd / cm)          | 62,992 x 51,05 x 46,33      |
| Unit Weight (lbs.)                  | 14.3                        |
| Unit Weight (kg)                    | 6.49                        |
| Weight Capacity - Stationary (kg)   | 91                          |
| Weight Capacity - Stationary (lbs.) | 200                         |
| Number of Vertical Mounting Rails   | 2                           |
| Assembly Required                   | Yes                         |
| FEATURES & SPECIFICATIONS           |                             |
| Pre-Installed Casters               | No                          |
| STANDARDS & COMPLIANCE              |                             |
| Product Compliance                  | RoHS; EIA/ECA-310-E         |
| WARRANTY & SUPPORT                  |                             |

|                                        |                         |
|----------------------------------------|-------------------------|
| Product Warranty Period<br>(Worldwide) | 5-year limited warranty |
|----------------------------------------|-------------------------|

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.