



Part Number : [1200270949](#)

Product Description : Nano-Change (M8) Single-Ended Cordset, 3 Poles, A-Coded, Female (90°) to Pigtail, with PNP LED Sensors, 0.25mm² PUR/PVC Cable, 10.0m (32.81') Length

Series Number : 120027

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 4030P1P02M100


Documents and Resources

Drawings

[1200270949_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate... per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120027
Description	Nano-Change (M8) Single-Ended Cordset, 3 Poles, A-Coded, Female (90°) to Pigtail, with PNP LED Sensors, 0.25mm ² PUR/PVC Cable, 10.0m (32.81') Length
IP Rating	IP68
Product Name	Nano-Change (M8)
Protocol	N/A
Type	Single Ended
UPC	883906224721

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	4.32mm (.170")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail

Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	PNP Sensors
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	305.240/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-30° TO +80°C
Wire/Cable Type	E152210
Wire Size (AWG)	N/A

This document was generated on Dec 29, 2025