

Multiband GNSS (GPS/GLONASS/BeiDou/Galileo) - FPC Antenna

AFAG3030-SG3

Request Samples



Check Inventory



30 x 30 x 0.2 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Features

- Multiband GNSS Coverage – GPS/GLONASS/BeiDou/Galileo
- Ultra-Low Profile
- Flexible Structure
- Peel-and-stick Mount
- Easy installation using IPEX Connector (Customizable Cable and Connector Options)

Applications

- IoT
- M2M
- Geofencing
- Remote Monitoring
- Logistics and Tracking
- Surveying and Mapping Systems

Electrical Specifications

Parameter		Specification			Unit
		Min	Typ	Max	
Operating Frequency*		1550		1620	MHz
Bandwidth			70		MHz
VSWR				2.5	
Gain	Peak		2 ~ 3		dBi
	Average		0~1		
Input Power				3	W
Impedance		50			Ω
Polarization		Vertical			
Radiation Pattern (Azimuth)		Omni-directional			

* All test measurements were conducted with the antenna on a 2 mm thick ABS surface. Please note that the operating frequency shifts with a change in housing material and thickness.

Mechanical Specifications

Parameter	Specification
Antenna Dimension	30 x 30 x 0.2 mm
Material	FPC
Mounting Type*	Adhesive Tape (3M 467MP)
RF Connector	IPEX - 1
RF Cable	Ø1.13 mm, L = 100 ± 5 mm

*Do not mount the antenna on a metal surface.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-03-20

ABRACON IS
ISO9001-2015
CERTIFIED

Multiband GNSS (GPS/GLONASS/BeiDou/Galileo) - FPC Antenna

AFAG3030-SG3

Request Samples



Check Inventory




30 x 30 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +85°C
RoHS Compliance	Yes
PB Free	Yes
MSL	Not Applicable
ESD Sensitive	No
Vibration	10 ~ 55 Hz with 1.5 mm amplitude 2 hrs

Product Dimension



Unit : mm

Multiband GNSS (GPS/GLONASS/BeiDou/Galileo) - FPC Antenna

AFAG3030-SG3

Request Samples



Check Inventory




30 x 30 x 0.2 mm

RoHS/RoHS II Compliant

MSL Level = N/A

Test Measurement - VSWR



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-03-20

ABRACON IS
ISO9001-2015
CERTIFIED

Multiband GNSS (GPS/GLONASS/BeiDou/Galileo) - FPC Antenna

AFAG3030-SG3

Request Samples




Check Inventory



30 x 30 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Radiation Characteristics



Multiband GNSS (GPS/GLONASS/BeiDou/Galileo) - FPC Antenna

AFAG3030-SG3

Request Samples




Check Inventory



30 x 30 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Efficiency



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-03-20

ABRACON IS
ISO9001-2015
CERTIFIED

Multiband GNSS (GPS/GLONASS/BeiDou/Galileo) - FPC Antenna

AFAG3030-SG3

Request Samples



Check Inventory



30 x 30 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Packaging Information

Number of Antenna/ Carton : 2000

Dimension of the Carton : 630 x 460 x 105 mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-03-20

ABRACON IS
ISO9001-2015
CERTIFIED