







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	12APR2021	J.S	I.Y
	A1	ECN-21-117700	15SEP2021	J.S	Z.Z



DETAIL Z
SCALE 5:1



2388278-1 AS SHOWN

1. MATERIAL : PA6-GF30 V-0 OR EQUIVALENCE RESIN.

2. PRODUCT DATE

3. LETTER-INSERTFOR THE REVISION STATUS OF THE MOULD

4. MATERIAL MARKING ACCORDING TO VDA260

5. BULK PACKAGING IN CORRUGATED BOX

6. MOULD CAVITY MARKING

7. TE LOGO

8. WARGAGE PERMITTED UP TO -1.5MM FROM NOMINAL SIZE

9. SUITALBE FOR TAB HOUISNG WITH FLANGE GROUP D, SEE PRODUCT GROUP DRAWING 1563709.

10. MARKING FOR SUITABLE SHEET METEAL THICKNESS(NOMINAL SIZE)

2388278-6	A	SLIDER 3.5MM	GREY	8.4	12.4	8.0	6.5
2388278-5	A	SLIDER 3MM	YELLOW	8.9	12.9	8.5	6.7
2388278-4	A	SLIDER 2.5MM	RED	9.4	13.4	9.0	6.9
2388278-3	A	SLIDER 1.5MM	GREY	10.4	14.4	10.0	7.4
2388278-2	A	SLIDER 1.2MM	ORANGE	10.7	14.7	10.3	7.5
2388278-1	A	SLIDER 1MM	NATURAL	10.9	14.9	10.5	7.6
PART NO	REV.	DESCRIPTION	COLOUR	DIM X	DIM Y	DIM Z	WEIGHT [g]

A1

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J. SHANG	12APR2021	TE Connectivity		
DIMENSIONS: mm			CHK C. WAN	12APR2021			
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD I. YIN	12APR2021	NAME SLIDE, GROUP D, TAB HOUSING		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH -			PRODUCT SPEC 108-94020		SIZE -		
MATERIAL PA6-GF30 V-0			APPLICATION SPEC 114-18756		CAGE CODE 00779		
			WEIGHT SEE TABLE A2		DRAWING NO C-2388278		
			CUSTOMER DRAWING		RESTRICTED TO -		
			SCALE 2:1		SHEET 1 OF 1		
					REV A1		