OMRON Industrial Automation



E2E-X4C112-M1

Proximity sensor, inductive, nickel-brass, short body, M12, shielded, 4 mm, DC, 3-wire, NPN NO, M12 connector

Downloaded from Arrow.com.

Specifications

Size	M12
Mounting type	Quasi-flush
Sensing distance	4 mm
Overall length of sensor	48 mm
Thread length	29 mm
Material housing	Brass, nickel plated
Output type	NPN
Operation mode	NO
Connection method	Connector M12
Cable specifications	-
IO-Link function	✖
IO-Link baud rate	Not Applicable
Degree of protection (IP)	IP67/IP69K

Accessories



Y92E-J12S18 OMS Mounting Sleeves e-jig for M12 Prox

Downloaded from Arrow.com.

Related products




M12 Connectors & Cordsets
Industrial connectors & cordsets for any application

Downloads

CAD Library



E2E NEXT
Datasheet
EN PDF 40 MB



E2E(Q) - Basic Models
Index list
EN PDF 7.27 MB



E2E(Q)-XB_XC_basic_model
Instruction Sheet
EN PDF 2.28 MB



IO-Link Series
Brochure
EN PDF 7.95 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 20 August, 2026. Click here for terms of use.

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU

Downloaded from Arrow.com.