

10135287 - 10X LF

LEAD-FREE DESIGNATION
ONLY WITH APPLICABLE
PLATING CODES

SEE NOTE 2

MODULE
DESCRIPTION

LETTER DESIGNATION REPRESENTED IN DASH NUMBER

BASE
MODULE

LEFT
POLARIZING
GUIDANCE
MODULE
(SEE SHEET 3)

N

J
(NO KEY)

A

B

C

D











E

F

G

H

NO KEY
NO GUIDE PIN



RIGHT
POLARIZING
GUIDANCE
MODULE
(SEE SHEET 2)

Z

Y
(NO KEY)

P

Q

R

S











T

U

V

W

NO KEY
NO GUIDE PIN



NOT TOOLED





PRELIMINARY




spec ref	---	dr	Tao Zhan	2015/05/26	projection	MM	size	A2	scale	8:1
tolerance std	ASME Y14.5M	eng	Tao Zhan	2016/03/14	chr	-	ecn no	-		
		appr	-	-	product family	AirMax VS2	rel level	Preliminary		
surface	-	linear	0.X	±.3	Amphenol FCi	title	AIRMAX VSe R.A. RECEPTACLE ASS'Y, 4 PAIR, 96 POS, 8 IMLA, 20MM, W/GUIDE/KEY	dwg no	10135287	rev
			0.XX	±.15						
			0.XXX	±.050						
		angular	0°	±°		cat. no.	-	Product - Customer Drw	sheet 1 of 4	

Amphenol
FCi

© 2016 AFci

RIGHT POLARIZATION WITH GUIDE



spec ref	---			dr	Tao Zhan	2015/05/26	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A2	scale	6:1							
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Tao Zhan	2016/03/14			ecn no	-	rel level	Preliminary							
ASME Y14.5M				chr	-	-							appr	-					
product family							AirMax VS2												
<div>surface</div> <div>-</div> <div></div>	linear	0.X	±.3	Amphenol FCi	title	AIRMAX VSe R.A. RECEPTACLE					dwg no	10135287		rev	1				
		0.XX	±.15			ASS'Y, 4 PAIR, 96 POS, 8 IMLA, 20MM, W/GUIDE/KEY													
		0.XXX	±.050			cat. no.						-				Product - Customer Drw		sheet 2 of 4	
		angular	0°			±°													

