


Ultra Fast NPT - IGBT®

The Ultra Fast 650V NPT-IGBT® family of products is the newest generation of IGBTs optimized for outstanding ruggedness and best trade-off between conduction and switching losses.

Features

- Low Saturation Voltage
- Low Tail Current
- RoHS Compliant 
- Short Circuit Withstand Rated
- High Frequency Switching
- Low Leakage Current



Combi (IGBT and Diode)



Unless stated otherwise, Microsemi discrete IGBTs contain a single IGBT die. This device is recommended for applications such as induction heating (IH), motor control, general purpose inverters and uninterruptible power supplies (UPS).

MAXIMUM RATINGS

All Ratings: $T_C = 25^\circ C$ unless otherwise specified.

Symbol	Parameter	Ratings	Unit
V_{CES}	Collector Emitter Voltage	650	V
V_{GE}	Gate-Emitter Voltage	± 30	
I_{C1}	Continuous Collector Current @ $T_C = 25^\circ C$	134	A
I_{C2}	Continuous Collector Current @ $T_C = 110^\circ C$	65	
I_{CM}	Pulsed Collector Current ^①	260	
SCWT	Short Circuit Withstand Time: $V_{CE} = 600V$, $V_{GE} = 15V$, $T_C = 125^\circ C$	10	μs
P_D	Total Power Dissipation @ $T_C = 25^\circ C$	595	W
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to 150	$^\circ C$
T_L	Max. Lead Temp. for Soldering: 0.063" from Case for 10 Sec.	300	

STATIC ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Min	Typ	Max	Unit
$V_{(BR)CES}$	Collector-Emitter Breakdown Voltage ($V_{GE} = 0V$, $I_C = 250\mu A$)	650			Volts
$V_{GE(TH)}$	Gate Threshold Voltage ($V_{CE} = V_{GE}$, $I_C = 1.0mA$, $T_J = 25^\circ C$)	3.5	5.0	6.5	
$V_{CE(ON)}$	Collector-Emitter On Voltage ($V_{GE} = 15V$, $I_C = 70A$, $T_J = 25^\circ C$)		1.9	2.4	
	Collector-Emitter On Voltage ($V_{GE} = 15V$, $I_C = 70A$, $T_J = 125^\circ C$)		2.4		
	Collector-Emitter On Voltage ($V_{GE} = 15V$, $I_C = 140A$, $T_J = 25^\circ C$)		2.6		
I_{CES}	Collector Cut-off Current ($V_{CE} = 650V$, $V_{GE} = 0V$, $T_J = 25^\circ C$) ^②		40	850	μA
	Collector Cut-off Current ($V_{CE} = 650V$, $V_{GE} = 0V$, $T_J = 125^\circ C$) ^②		500		
I_{GES}	Gate-Emitter Leakage Current ($V_{GE} = \pm 20V$)			± 250	nA



CAUTION: These Devices are Sensitive to Electrostatic Discharge. Proper Handling Procedures Should Be Followed.

DYNAMIC CHARACTERISTICS


APT70GR65B2SCD30

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
C_{ies}	Input Capacitance	Capacitance $V_{GE} = 0V, V_{CE} = 25V$ $f = 1MHz$		4250		pF
C_{oes}	Output Capacitance			847		
C_{res}	Reverse Transfer Capacitance			415		
V_{GEP}	Gate to Emitter Plateau Voltage	Gate Charge $V_{GE} = 15V$ $V_{CE} = 325V$ $I_C = 70A$		7.0		V
$Q_g^{(3)}$	Total Gate Charge			226	305	nC
Q_{ge}	Gate-Emitter Charge			26	35	
Q_{gc}	Gate- Collector Charge			104	140	
$t_{d(on)}$	Turn-On Delay Time	Inductive Switching (25°C) $V_{CC} = 433V$ $V_{GE} = 15V$ $I_C = 70A$ $R_G = 4.3\Omega^{(4)}$ $T_J = +25^\circ C$		19		ns
t_r	Current Rise Time			45		
$t_{d(off)}$	Turn-Off Delay Time			170		
t_f	Current Fall Time			67		
$E_{on2}^{(5)}$	Turn-On Switching Energy			1790	2685	μJ
$E_{off}^{(6)}$	Turn-Off Switching Energy			1460	1970	
$t_{d(on)}$	Turn-On Delay Time	Inductive Switching (125°C) $V_{CC} = 433V$ $V_{GE} = 15V$ $I_C = 70A$ $R_G = 4.3\Omega^{(4)}$ $T_J = +125^\circ C$		19		ns
t_r	Current Rise Time			45		
$t_{d(off)}$	Turn-Off Delay Time			190		
t_f	Current Fall Time			74		
$E_{on2}^{(5)}$	Turn-On Switching Energy			1760	2640	μJ
$E_{off}^{(6)}$	Turn-Off Switching Energy			1720	2580	

THERMAL AND MECHANICAL CHARACTERISTICS

Symbol	Characteristic	Min	Typ	Max	Unit
$R_{\theta JC}$	Junction to Case Thermal Resistance			.21	°C/W
$R_{\theta JA}$	Junction to Ambient Thermal Resistance			40	
W_T	Package Weight		.22 6.2		oz g

- 1 Repetitive Rating: Pulse width and case temperature limited by maximum junction temperature.
 - 2 Pulse test: Pulse Width < 380μs, duty cycle < 2%.
 - 3 See Mil-Std-750 Method 3471.
 - 4 R_G is external gate resistance, not including internal gate resistance or gate driver impedance. (MIC4452)
 - 5 E_{on2} is the energy loss at turn-on and includes the charge stored in the freewheeling diode.
 - 6 E_{off} is the clamped inductive turn-off energy measured in accordance with JEDEC standard JESD24-1.
- Microsemi reserves the right to change, without notice, the specifications and information contained herein.



TYPICAL PERFORMANCE CURVES

AP70GR65B2SCD30




FIGURE 2, Max Frequency vs Current ($T_{case} = 75^{\circ}C$)




FIGURE 3, Saturation Voltage Characteristics ($T_J = 25^{\circ}C$)




FIGURE 4, Output Characteristics ($T_J = 25^{\circ}C$)




FIGURE 5, On State Voltage vs Junction Temperature




FIGURE 6, Transfer Characteristics




FIGURE 7, On State Voltage vs Gate-to-Emitter Voltage




FIGURE 8, Breakdown Voltage vs Junction Temperature




FIGURE 9, DC Collector Current vs Case Temperature

TYPICAL PERFORMANCE CURVES

APT70GR65B2SCD30




FIGURE 10, Capacitance vs Collector-To-Emitter Voltage




FIGURE 11, Gate charge




FIGURE 12, Turn-On Time vs Collector Current




FIGURE 13, Turn-Off Time vs Collector Current




FIGURE 14, Energy Loss vs Collector Current




FIGURE 15, Energy Loss vs Gate Resistance




FIGURE 16, Switching Energy vs Junction Temperature




FIGURE 17, Minimum Switching Safe Operating Area

ZERO RECOVERY LOW LEAKAGE SIC ANTI-PARALLEL DIODE

MAXIMUM RATINGS All Ratings: $T_C = 25^\circ\text{C}$ unless otherwise specified.

Symbol	Characteristic / Test Conditions	Ratings	Unit
I_F	Maximum D.C. Forward Current	$T_C = 25^\circ\text{C}$	46
		$T_C = 85^\circ\text{C}$	30
I_{FSM}	Non-Repetitive Forward Surge Current ($T_J = 25^\circ\text{C}$, $t_p = 10\text{ms}$, Half Sine)	247	Amps

STATIC ELECTRICAL CHARACTERISTICS

Symbol	Characteristic / Test Conditions	Min	Typ	Max	Unit
V_F	Forward Voltage		$I_F = 30\text{A}$, $T_J = 25^\circ\text{C}$	1.5	Volts
			$I_F = 30\text{A}$, $T_J = 150^\circ\text{C}$	1.9	
Q_c	Total Capacitive Charge $V_R = 325\text{V}$, $I_F = 30\text{A}$, $di/dt = -500\text{A}/\mu\text{s}$, $T_J = 25^\circ\text{C}$		150		nC
C_T	Junction Capacitance $V_R = 1\text{V}$, $T_J = 25^\circ\text{C}$, $f = 1\text{MHz}$		945		pF
	Junction Capacitance $V_R = 200\text{V}$, $T_J = 25^\circ\text{C}$, $f = 1\text{MHz}$		138		
	Junction Capacitance $V_R = 400\text{V}$, $T_J = 25^\circ\text{C}$, $f = 1\text{MHz}$		105		




FIGURE 18. MAXIMUM EFFECTIVE TRANSIENT THERMAL IMPEDANCE, JUNCTION-TO-CASE vs. PULSE DURATION




FIGURE 19. Forward Current vs. Forward Voltage




FIGURE 20. Maximum Forward Current vs. Case Temperature




Figure 21. Maximum Power Dissipation vs. Case Temperature




Figure 22. Reverse Recovery Charge vs. V_R





Figure 23. Junction Capacitance vs. Reverse Voltage

T-MAX® (B2) Package Outline



These dimensions are equal to the TO-247 without the mounting hole.
Dimensions in Millimeters and (Inches)

The information contained in the document (unless it is publicly available on the Web without access restrictions) is PROPRIETARY AND CONFIDENTIAL information of Microsemi and cannot be copied, published, uploaded, posted, transmitted, distributed or disclosed or used without the express duly signed written consent of Microsemi. If the recipient of this document has entered into a disclosure agreement with Microsemi, then the terms of such Agreement will also apply. This document and the information contained herein may not be modified, by any person other than authorized personnel of Microsemi. No license under any patent, copyright, trade secret or other intellectual property right is granted to or conferred upon you by disclosure or delivery of the information, either expressly, by implication, inducement, estoppels or otherwise. Any license under such intellectual property rights must be approved by Microsemi in writing signed by an officer of Microsemi.

Microsemi reserves the right to change the configuration, functionality and performance of its products at anytime without any notice. This product has been subject to limited testing and should not be used in conjunction with life-support or other mission-critical equipment or applications. Microsemi assumes no liability whatsoever, and Microsemi disclaims any express or implied warranty, relating to sale and/or use of Microsemi products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right. Any performance specifications believed to be reliable but are not verified and customer or user must conduct and complete all performance and other testing of this product as well as any user or customers final application. User or customer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is the customer's and user's responsibility to independently determine suitability of any Microsemi product and to test and verify the same. The information contained herein is provided "AS IS, WHERE IS" and with all faults, and the entire risk associated with such information is entirely with the User. Microsemi specifically disclaims any liability of any kind including for consequential, incidental and punitive damages as well as lost profit. The product is subject to other terms and conditions which can be located on the web at <http://www.microsemi.com/legal/tnc.asp>