



Miniature Pushbutton Switches

3

Specifications:


Contact resistance:	<10 mΩ
Insulation resistance:	>100 MΩ
Dielectric strength:	500 V, 50 Hz for the duration of 1 minute
Operating temperature:	-10 °C to +60 °C
Operating force:	3 N ± 1 N
Mechanical life:	minimum 30 000 operations
Material:	Contacts: Phosphor-Bronze, silver-plated Terminals: Brass, silver-plated Case: ABS Actuator: POM
Mounting:	on pc-board
Timing:	non-shorting
Travel:	4.7 mm, locking travel: 3.0 mm
Soldering conditions:	wave-soldering – max. 5 s, 260 °C

Models:

Switching function:


MPBS 22H01L-F14

on – on



MPBS 62H01-F14

on – mom



Ordering Code:

MPBS - ☐ 2H01 ☐ - F14

Poles:

- ☒ 2 poles
- ☒ 4 poles
- ☒ 6 poles

Switching mode:

- ☐ on – mom
- ☒ on – on