




[+ HARNESSING](#)
[HEAT SHRINK BOOTS](#)



✓ Active
TE CONNECTIVITY (TE)
202A174-3-0
[Raychem](#) | [CAP](#) , [CRPS](#)

202A174-3-0
TE Internal Number: 814300-000
Alias ID: 8-1196337-7

[EU RoHS Compliant](#)
[EU ELV Compliant](#)
Molded Part Shape Straight
Lipped No

Operating Temperature Range (°C) -55 – 135
Fluid/Chemical Resistance Suitable for occasional exposure to fluids
Adhesive Options S1006 Separate Adhesive, -55°C to +135°C (-67°F to + 275°F), S1017 Separate Adhesive, -20°C to +60°C (-4°F to +140°F), S1030 Separate Adhesive, -80°C to +80°C (-112°F to +176°F)

 **PRODUCT DRAWING**
[English](#)

DOCUMENTATION

Product Drawings
Boot, Straight, Overexpanded
PDF
English

Product Specifications
Product Specification
Thermofit Polyolefin Molded Components Flame-Retarded, Semi-Rigid, Heat-Shrinkable
PDF
English

Product Environmental Compliance
Safety Data Sheet

EPS Heat Shrinkable Polymeric Products

PDF

French

EPS Heat Shrinkable Polymeric Products

PDF

Italian

EPS Heat Shrinkable Polymeric Products

PDF

Dutch

EPS Heat Shrinkable Polymeric Products

PDF

Danish

EPS Heat Shrinkable Polymeric Products

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

German

EPS Heat Shrinkable Polymeric Products

PDF

Norwegian

EPS Heat Shrinkable Polymeric Products

PDF

Spanish

EPS Heat Shrinkable Polymeric Products

PDF

Swedish

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Molded Part Shape Straight
- Molded Part Type Molded Boot

Configuration Features

- Lipped No

Body Features

- Material Systems Code 10
- Adhesive Pre-Coat No

Dimensions

Cable Diameter Range 16 – 48.3 mm [.63 – 1.9 in]
Wire/Cable Outside Diameter .71 in, .79 in, .87 in, .94 in, 1.02 in, 1.1 in, 18 mm, 20 mm, 22 mm, 24 mm, 26 mm, 28 mm
Connector or Backshell Outside Diameter 1.57 in, 1.69 in, 1.81 in, 1.93 in, 40 mm, 43 mm, 46 mm, 49 mm

Usage Conditions

Operating Temperature Range (°C) -55 – 135

Industry Standards

Approved Standards BS-G-198-5-DA, DEF Std 59-97 Issue 3 Type DA, SAE AS I 81765/1, Type I, UL 224, File E85381

Other

Fluid/Chemical Resistance Suitable for occasional exposure to fluids
Adhesive Options S1006 Separate Adhesive, -55°C to +135°C (-67°F to + 275°F), S1017 Separate Adhesive, -20°C to +60°C (-4°F to +140°F), S1030 Separate Adhesive, -80°C to +80°C (-112°F to +176°F)

Statement of Compliance

Statement of Compliance
PDF