



3SBH5004K6 Product Details

[Share](#) [Print](#) [Email](#)


3SBH5004K6
(1617348-1)

TE Internal Number: 1617348-1

 **Active**

Military/Aerospace High Performance Relays

Not EU RoHS or ELV Compliant


Product Highlights:

- 3SBH 1/5-Size Relay Series
- Input Voltage = 26.5 VDC
- Contact - Arrangement = 4 Form C, 4PDT, 4 C/O
- Contact - Rated Current = 2 A
- Non Polarized, Monostable Coil - Magnetic System

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Series](#) = 3SBH 1/5-Size Relay
- MOSFET Driver = Without
- Termination Type = PC Pins

Mechanical Attachment:

- Mounting Options = PC Board

Electrical Characteristics:

- Input Voltage (VDC) = 26.5
- Contact - Rated Current (A) = 2
- Coil Suppression Diode = With
- Coil Polarity Protection Diode = Without
- Transistor Driver = Without
- Coil - Resistance (Ω) = 720
- Coil Power Measurement = Milliwatts
- Coil - Rated Power, DC (mW) = 975
- Actuating System = DC
- Shock = 100G's, 11ms
- Vibration = 30G's, 10 to 3000Hz

Body Features:

- Enclosure Type = Hermetically Sealed

Configuration Features:

- [Contact - Arrangement](#) = 4 Form C, 4PDT, 4 C/O
- Coil - Magnetic System = Non Polarized, Monostable

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

Conditions for Usage:

- Temperature Range ($^{\circ}\text{C}$) = -65 - +125

Other:

- Brand = CII

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

