


This document is the property of Amphenol Corporation and is delivered on the understanding that it is not to be reproduced, stored in a retrieval system, or in part, for manufacture or sale by anyone other than Amphenol Corporation or its authorized agents. No right is granted to disclose or to use any information in this document.



RECOMMENDED P.C.B LAYOUT
(TOLERANCE + / -0.03)

Customer drawing



DIM.S	A	B	C	D	Pitch
SHELL					
9	30.70	16.40	25.00	10.96	2.74
15	39.00	24.80	33.30	19.18	2.74
25	52.90	38.50	47.00	33.12	2.77
37	69.20	54.90	63.50	49.68	2.77

REVISONS		
SYM	ECN	DATE
1		06/18/08

D-SUB TECHNICAL DATA

SHELL : Steel 2.5um(100u") min tin over 1.25um(50u") min nickel
BODY : Glass filled thermoplastic.
CONTACTS : Flame retardant to UL94 V-0 Color Black Brass
BRACKET : 0.1um(4u") min gold over 1.25um(50u") min nickel
ELECTRICAL : Steel,100u" min tin over 50u" min nickel
Voltage rating : 300 V RMS at 50 Hz
Current rating 7.5A.
Insulation resistance >5000 M Ohms
Contact resistance 20 mohms max.
CLIMATIC : Temperature range -55 °C up to 85°C
Damp heat 21 days(40 °C-95% HR)
MARKING : Amphenol-...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L77D X XX S 1AMN

L: RoHS Compliance

77D: tinned shell for receptacle

Shell Size : E,A,B,C

Configuration: 09,15,25,37

Right angle connector:
European footprint
metal bracket
1AMN=X=2.54

Contact type:
S: Female

UNLESS OTHERWISE SPECIFIED		APPROVAL		DATE	
TOLERANCES		DRAWN		CHECKED	
U.S.		METRIC		CHECKED	
X		+/-		0.50	
XX		+/-		0.30	
XXX		+/-		0.20	
FRACTIONS		+/-		2'	
ANGLES		+/-		2'	
FOR MATERIALS AND FINISHES		DRAWING FILE :		ANGLE OF PROJECTION	
SEE NOTES		REMOVE SHARP EDGES		U.S.	
DIMENSIONS		TOLERANCES		MM	
U.S.		TOLERANCES		MM	

Amphenol

TITLE		REV.	
machined contacts connector, D series		1	
SIZE		DRAWING NO.	
A4		C L77DXXXS1AMN	
SCALE		SHEET 1 OF 1	