

Features

- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisture Sensitivity Level 1
- Halogen Free. "Green" Device (Note 1)
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)

Maximum Ratings


- Operating Junction Temperature Range : -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Thermal Resistance: 62.5°C/W Junction to Ambient

Parameter		Symbol	Rating	Unit
Total Power Dissipation		P _D	2.0	W
N-Channel MOSFET				
Drain-Source Voltage		V _{DS}	30	V
Gate-Source Voltlage		V _{GS}	±20	V
Continuous Drain Current ^(Note 2)	T _A =25°C	I _D	6.5	A
	T _A =70°C		5.4	A
Pulsed Drain Current ^(Note 3)		I _{DM}	26	A
P-Channel MOSFET				
Drain-Source Voltage		V _{DS}	-30	V
Gate-Source Voltlage		V _{GS}	±20	V
Continuous Drain Current ^(Note 2)	T _A =25°C	I _D	-5.0	A
	T _A =70°C		-4.1	A
Pulsed Drain Current ^(Note 3)		I _{DM}	-20	A

Note:


1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
2. These Tests Are Performed With Infinite Heat Sink.
3. Pulse Width By Max. Junction Temperature.

Internal Structure and Marking Code




Dual N&P-Channel MOSFET

SOP-8



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.053	0.069	1.35	1.75	
B	0.004	0.010	0.10	0.25	
C	0.053	0.061	1.35	1.55	
D	0.013	0.020	0.33	0.51	
E	0.007	0.010	0.17	0.25	
F	0.185	0.200	4.70	5.10	
G	0.050		1.270		TYP.
H	0.228	0.244	5.80	6.20	
J	0.150	0.157	3.80	4.00	
K	0.016	0.050	0.40	1.27	
θ	0°	8°	0°	8°	

Suggested Solder Pad Layout



N-Channel MOSFET Electrical Characteristics @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS}=0V, I_D=250\mu A$	30			V
Gate-Source Leakage Current	I_{GSS}	$V_{DS}=0V, V_{GS}=\pm 20V$			± 100	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=30V, V_{GS}=0V$			1	μA
Gate-Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	1.2	1.6	2.4	V
Drain-Source On-Resistance ^(Note 4)	$R_{DS(on)}$	$V_{GS}=10V, I_D=5A$			30	m Ω
		$V_{GS}=4.5V, I_D=5A$			40	
Diode Forward Voltage ^(Note 4)	V_{SD}	$V_{GS}=0V, I_S=5A$			1.2	V
Forward Transconductance	g_{FS}	$V_{DS}=5V, I_D=5A$	4			S
Dynamic Characteristics						
Input Capacitance ^(Note 5)	C_{iss}	$V_{DS}=15V, V_{GS}=0V, f=1MHz$		255		pF
Output Capacitance ^(Note 5)	C_{oss}			45		
Reverse Transfer Capacitance ^(Note 5)	C_{rss}			35		
Total Gate Charge ^(Note 4)	Q_g	$V_{DD}=15V, V_{GS}=10V, I_D=5A$		5.2		nC
Gate-Source Charge ^(Note 5)	Q_{gs}			0.85		
Gate-Drain Charge ^(Note 5)	Q_{gd}			1.3		
Turn-On Delay Time ^(Note 4)	$t_{d(on)}$	$V_{DD}=15V, V_{GS}=10V$ $R_L=2.5\Omega, R_G=3.3\Omega$		4.5		ns
Turn-On Rise Time ^(Note 5)	t_r			2.5		
Turn-Off Delay Time ^(Note 5)	$t_{d(off)}$			14.5		
Turn-Off Fall Time ^(Note 5)	t_f			3.5		

P-Channel Electrical Characteristics @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS}=0V, I_D=-250\mu A$	-30			V
Gate-Source Leakage Current	I_{GSS}	$V_{DS}=0V, V_{GS}=\pm 20V$			± 100	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=-30V, V_{GS}=0V$			1	μA
Gate-Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=-250\mu A$	-1	-1.6	-2.5	V
Drain-Source On-Resistance ^(Note 4)	$R_{DS(on)}$	$V_{GS}=-10V, I_D=-4A$			60	m Ω
		$V_{GS}=-4.5V, I_D=-4A$			90	
Diode Forward Voltage ^(Note 4)	V_{SD}	$V_{GS}=0V, I_S=-5A$			-1.2	V
Forward Transconductance	g_{FS}	$V_{DS}=-5V, I_D=-5A$	4			S
Dynamic Characteristics						
Input Capacitance ^(Note 5)	C_{iss}	$V_{DS}=-15V, V_{GS}=0V, f=1MHz$		520		pF
Output Capacitance ^(Note 5)	C_{oss}			100		
Reverse Transfer Capacitance ^(Note 5)	C_{rss}			65		
Total Gate Charge ^(Note 4)	Q_g	$V_{DD}=-15V, V_{GS}=-10V, I_D=-5A$		9.2		nC
Gate-Source Charge ^(Note 5)	Q_{gs}			1.6		
Gate-Drain Charge ^(Note 5)	Q_{gd}			2.2		
Turn-On Delay Time ^(Note 4)	$t_{d(on)}$	$V_{DD}=-15V, V_{GS}=-10V$ $RL=2.3\Omega, RG=6\Omega$		7.5		ns
Turn-On Rise Time ^(Note 5)	t_r			5.5		
Turn-Off Delay Time ^(Note 5)	$t_{d(off)}$			19		
Turn-Off Fall Time ^(Note 5)	t_f			7		

Note 4. Pulse Test : Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 2\%$.

5. Guaranteed by Design, Not Subject to Production Testing.

N-Channel MOSFET Curve Characteristics

Fig. 1 - Output Characteristics




Fig. 2 - Transfer Characteristics




Fig. 3 - $R_{DS(ON)} - I_D$




Fig. 4 - $R_{DS(ON)} - V_{GS}$





Fig. 5 - $I_S - V_{SD}$



P-Channel MOSFET Curve Characteristics

Fig. 1 - Output Characteristics




Fig. 2 - Transfer Characteristics




Fig. 3 - $R_{DS(ON)} - I_D$




Fig. 4 - $R_{DS(ON)} - V_{GS}$





Fig. 5 - $I_S - V_{SD}$



Ordering Information

Device	Packing
Part Number-TP	Tape&Reel: 4Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.