

- Compact metal case with screw terminal block
- Universal input 90-264 VAC
- I/O reinforced isolation 3000 VAC
- Active power factor correction >0.9
- Internal EN 55032 class B filter
- High efficiency up to 89%
- Operating temperature range -30°C to +70°C
- Short circuit, overvoltage and overload protection
- IEC/EN/UL 62368-1 safety approvals
- 3-year product warranty



The TXN 350 is a cost efficient, metal enclosed AC/DC power supplies series and is designed for industrial applications. With a low-profile metal case and screw terminal block connection, they are easy to install in any equipment. Active PFC (>0.9), internal EMC filter, high IO-isolation and wide temperature range qualify them for numerous industrial applications. All models within the TXN 350 series have universal input (90-264 VAC) and comply with the latest industrial standard IEC/EN/UL 62368-1, European EMC standards and the Low Voltage Directive (LVD).

Models

Order Code	Output Power max.	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TXN 350-112	325 W	12 VDC (10.0 - 13.2 VDC)	27'000 mA	86 %
TXN 350-115	330 W	15 VDC (13.5 - 15.5 VDC)	22'000 mA	87 %
TXN 350-124	350 W	24 VDC (20.0 - 26.4 VDC)	14'600 mA	88 %
TXN 350-148		48 VDC (41.0 - 56.0 VDC)	7'400 mA	89 %

Options

TXN-AUX2	- Optional Cable: www.tracopower.com/overview/txn-aux2
----------	--

Input Specifications

Input Voltage	- AC Range	Operational Range: 90 - 264 VAC (Full Range) Rated Range: 100 - 240 VAC (Full Range)
	- DC Range	Operational Range: 140 - 340 VDC (Designed for, no certification) Polarity: +DC: L / -DC: N
Input Frequency		Operational Range: 47 - 63 Hz Certified: 50/60 Hz
Power Consumption	- No load & Vin = 230 VAC	6 W max.
	- No load & Vin = 115 VAC	6 W max.
Input Current	- Full load & Vin = 230 VAC	2.2 A max.
	- Full load & Vin = 115 VAC	4.5 A max.
Input Inrush Current	- At 230 VAC	60 A max.
	- At 115 VAC	30 A max.
Power Factor	- At 230 VAC	0.9 min. (Active Power Factor Correction)
	- At 115 VAC	0.95 min. (Active Power Factor Correction)
Input Protection		T 6.3 A / 250 VAC (Internal Fuse in L)
Recommended Input Fuse		(The need of an external fuse has to be assessed in the final application.)

Output Specifications

Output Voltage Adjustment		12 VDC model: 10.0 - 13.2 VDC
		15 VDC model: 13.5 - 15.5 VDC
		24 VDC model: 20.0 - 26.4 VDC
		48 VDC model: 41.0 - 56.0 VDC
		(By trim potentiometer) Output power must not exceed rated power!
Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax)	0.5% max.
	- Load Variation (10 - 90%)	1% max.
Ripple and Noise (20 MHz Bandwidth)	12 VDC model:	150 mVp-p max. (w/ 0.1 µF 47 µF)
	15 VDC model:	150 mVp-p max. (w/ 0.1 µF 47 µF)
	24 VDC model:	150 mVp-p max. (w/ 0.1 µF 47 µF)
	48 VDC model:	240 mVp-p max. (w/ 0.1 µF 47 µF)
Capacitive Load	12 VDC model:	42'300 µF max.
	15 VDC model:	19'800 µF max.
	24 VDC model:	19'800 µF max.
	48 VDC model:	6'100 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.03 %/K max.
Hold-up Time	- At 230 VAC	8 ms min.
	- At 115 VAC	8 ms min.
Start-up Time	- At 230 VAC	1.5 s max.
	- At 115 VAC	1.5 s max.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		110 - 160% of Iout max.
Overvoltage Protection		110 - 140% of Vout nom.

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1
	- Certification Documents	www.tracopower.com/txn350-safety-cert
Protection Class		Class I (Prepared): Connection to PE

See application note: www.tracopower.com/info/protection-class.pdf

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Pollution Degree	PD 2
Over Voltage Category	OVC II

EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 55032 class B (internal filter)	
	- Radiated Emissions	EN 55032 class B (internal filter)	
	- Harmonic Current Emissions	EN 61000-3-2, class A	
	- Voltage Fluctuations & Flicker	EN 61000-3-3	
EMS (Immunity)	- Electrostatic Discharge	EN 55035 (Multimedia) Air: EN 61000-4-2, ±8 kV, perf. criteria B Contact: EN 61000-4-2, ±4 kV, perf. criteria B EN 61000-4-3, 10 V/m, perf. criteria A EN 61000-4-4, ±2 kV, perf. criteria A	
	- RF Electromagnetic Field	L to L: EN 61000-4-5, ±1 kV, perf. criteria B L to PE: EN 61000-4-5, ±2 kV, perf. criteria B	
	- EFT (Burst) / Surge	EN 61000-4-6, 10 Vrms, perf. criteria B	
	- Conducted RF Disturbances	Continuous: EN 61000-4-8, 30 A/m, perf. criteria A	
	- PF Magnetic Field	230 VAC / 50 Hz: EN 61000-4-11	
	- Voltage Dips & Interruptions	30%, 25 periods, perf. criteria C >95%, 0.5 periods, perf. criteria B >95%, 250 periods, perf. criteria C	
	EMC / Environmental	- Certification Documents	www.tracopower.com/txn350-emc-cert

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-30°C to +70°C
	- Storage Temperature	-40°C to +80°C
Power Derating	- High Temperature	2 %/K above 50°C
	- Low Input Voltage	1 %/V below 110 VAC
		See application note: www.tracopower.com/txn350-cc
Over Temperature Protection Switch Off	- Protection Mode	Automatic recovery
	- Measurement Point	Internal IC temperature
Cooling System		Forced air cooling (with internal fan)
Remote Control	- Voltage Controlled Remote (passive = on)	On: < 0.6 VDC or open circuit or short circuit Off: 4 to 10 VDC Refers to '+Remote' and '-Remote' Pin
	- Remote Pin Input Current	0.5 to 2.5 mA
Altitude During Operation		5'000 m max.
Regulator Topology		Forward Converter
Switching Frequency		75 kHz typ. (PWM)
Insulation System		Reinforced Insulation
Isolation Test Voltage	- Input to Output, 60 s	4'000 VDC
	- Input to Case or PE, 60 s	2'500 VDC
	- Output to Case or PE, 60 s	750 VDC
Isolation Resistance	- Input to Output, 500 VDC	100 MΩ min.
Leakage Current (at 240 VAC / 60 Hz)	- Earth Leakage Current	3.5 mA max.
Reliability	- Calculated MTBF	230'600 h (MIL-HDBK-217F, ground benign)
Washing Process		Not allowed
Environment	- Vibration	2 g, 3 axis, 60 min, 10-500 Hz, 10 min/cycle
	- Mechanical Shock	20 g, 3 axis, 3 shocks
Housing Material		Aluminum (Chassis)
Housing Type		Metal Case
Mounting Type		Chassis Mount
Connection Type		Screw Terminal


All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Weight	800 g
Status Indicator	Indicated by green LED
Sense Function	(0.2 V max.)
Environmental Compliance	- REACH Declaration www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant - RoHS Declaration www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7(a), 7(c)-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (05A rule)) - SCIP Reference Number
	163c9061-aae2-44f9-bd9a-e9bec4763d65

Additional Information

Supporting Documents	www.tracopower.com/overview/txn350
Frequently Asked Questions	www.tracopower.com/glossary-faq
Glossary	www.tracopower.com/info/glossary.pdf

Outline Dimensions



Pin connectors

Input/Output		AUX	
Pin	Function	Pin	Function
1	+Vout	1	+Remote
2		2	-Remote
3		3	+Sense
4	-Vout	4	-Sense
5			
6			
7	PE		
8	AC (N)		
9	AC (L)		

Input/Output:
Wire dimension range: 22 - 12 AWG
0.324 - 3.31 mm²