

121-193


Annular Polymer-Core Convuluted Tubing with Double External Braid and Jacket



Series 72
Annular Tubing

For environmental EMI/RFI applications with high dB shielding requirements

How To Order




B

Table I - Dash Number/Diameter			
Dash No	A Inside Dia		B Outside Dia
	Min	Max	Max
06	.17 (4.3)	.19 (4.8)	.57 (14.5)
09	.24 (6.1)	.28 (7.1)	.67 (17.0)
12	.33 (8.4)	.37 (9.4)	.77 (19.5)
14	.40 (10.1)	.44 (11.2)	.84 (21.3)
16	.45 (11.4)	.50 (12.7)	.91 (23.1)
20	.57 (14.5)	.62 (15.7)	1.02 (25.9)
24	.69 (17.5)	.75 (19.1)	1.19 (30.2)
28	.81 (20.6)	.87 (22.1)	1.33 (33.8)
32	.93 (23.6)	1.00 (25.4)	1.45 (36.8)
40	1.18 (30.0)	1.25 (31.8)	1.69 (42.9)
48	1.43 (36.3)	1.50 (38.1)	1.96 (49.8)
52	1.56 (39.6)	1.63 (41.4)	2.10 (53.3)

Table II - Tubing Option	
Y	Kynar/Thermally stabilized
V	PVDF/Not thermally stabilized
S	G-FLEX Siltem/Medium duty - natural color only

Table IV - Jacket Option	
N	Neoprene
H	Hypalon
E	EPDM
V	Viton
B	Duralectric, black
G	Bluejacket, Gray
TN	Duralectric, Desert Tan

Table III - Shield/Braid Option	
T	Tin/Copper
C	Stainless Steel
N	Nickel Copper
L	AarmorLite™
D	Dacron
M	Nomex
E	AmberStrand® 100%
F	AmberStrand® 75%/25%



Standard Shipping Package	
Dash No.	Max Length Per Pkg.
09& 12	200 ft (60m)
16 - 52	100 ft (30m)

Packaging

121-193 braided and jacketed conduit is typically supplied in 50 foot lengths. Longer lengths are available—consult factory for additional information. Unless otherwise specified, Glenair packages optimal lengths of product based on weight, size, and commercial carrier specifications. If necessary, consult factory for additional information on package weight restrictions.