SIEMENS

Data sheet 6EP1336-3BA10



SITOP PSU8200/1ACDC/24VDC/20A

SITOP PSU8200 20 A stabilized power supply input: 120-230 V AC 110-220 V DC output: 24 V DC/20 A

General information	
Technical Product Detail Page	https://i.siemens.com/1P6EP1336-3BA10
input	
type of the power supply network	1-phase and 2-phase AC or DC
supply voltage at AC	
● minimum rated value	120 V
● maximum rated value	230 V
● initial value	85 V
● full-scale value	275 V
supply voltage at AC	temperature derating necessary at Uin<100 V AC or DC at 50 °C; additional derating at Uin<100 V: Uin=95 V Pa max=460 W, Uin=90 V Pa max=440 W, Uin=85 V Pa max=420 W
supply voltage at DC	110 ... 220 V
input voltage at DC	88 ... 350 V
wide range input	Yes
buffering time for rated value of the output current in the event of power failure minimum	20 ms
operating condition of the mains buffering	at Vin = 230 V
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
● at rated input voltage 120 V	4.6 A
● at rated input voltage 230 V	2.5 A
current limitation of inrush current at 25 °C maximum	20 A
I2t value maximum	5 A²·s
fuse protection type	Yes
fuse protection type in the feeder	Recommended miniature circuit breaker at 1-phase operation: 10 A characteristic C; required at 2-phase operation: circuit breaker 2-pole connected or circuit breaker 3RV2711-1HD10 (UL 489) at 120 V or 3RV2711-1ED10 (UL 489) at 230 V
output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
● at output 1 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	24 ... 28 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
● on slow fluctuation of input voltage	0.1 %

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

● on slow fluctuation of ohm loading	0.3 %
residual ripple	
● maximum	100 mV
● typical	80 mV
voltage peak	
● maximum	200 mV
● typical	100 mV
display version for normal operation	Green LED for 24 V OK
type of signal at output	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	1.5 s
voltage increase time of the output voltage	
● typical	250 ms
output current	
● rated value	20 A
● rated range	0 ... 20 A; +60 ... +70 °C: Derating 3%/K
supplied active power typical	480 W
short-term overload current	
● at short-circuit during operation typical	60 A
duration of overloading capability for excess current	
● at short-circuit during operation	25 ms
constant overload current	
● on short-circuiting during the start-up typical	30 A
bridging of equipment	Yes; switchable characteristic
number of parallel-switched equipment resources for increasing the power	2
efficiency	
efficiency in percent	94 %
power loss [W]	
● at rated output voltage for rated value of the output current typical	31 W
closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.5 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	1 %
setting time	
● load step 50 to 100% typical	1 ms
● load step 100 to 50% typical	1 ms
setting time	
● maximum	5 ms
protection and monitoring	
design of the overvoltage protection	< 31.8 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Alternatively, constant current characteristic approx. 21.5 A or latching shutdown
● typical	21.5 A
overcurrent overload capability	
● in normal operation	overload capability 150 % Iout rated up to 5 s/min
enduring short circuit current RMS value	
● typical	21.5 A
display version for overload and short circuit	LED yellow for "overload", LED red for "latching shutdown"
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I
leakage current	
● maximum	3.5 mA
● typical	1 mA
protection class IP	IP20

© Copyright Siemens
Downloaded from Arrow.com.

EMC	
standard	
● for emitted interference	EN 55022 Class B
● for mains harmonics limitation	EN 61000-3-2
● for interference immunity	EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
● CE marking	Yes
● UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
● UKCA marking	Yes
● EAC approval	Yes
● Regulatory Compliance Mark (RCM)	Yes
● NEC Class 2	No
● SEMI F47	Yes
type of certification	
● BIS	Yes; R-41183539
● CB-certificate	Yes
MTBF at 40 °C	583 500 h
standards, specifications, approvals hazardous environments	
certificate of suitability	
● IECEx	No
● ATEX	No
● ULhazloc approval	No
● FM registration	No
standards, specifications, approvals marine classification	
shipbuilding approval	Yes
Marine classification association	
● American Bureau of Shipping Europe Ltd. (ABS)	Yes
● French marine classification society (BV)	No
● Det Norske Veritas (DNV)	Yes
● Lloyds Register of Shipping (LRS)	No
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
● total	814.2 kg
● during manufacturing	28.7 kg
● during operation	785 kg
● after end of life	0.24 kg
ambient conditions	
ambient temperature	
● during operation	-25 ... +70 °C; With natural convection; startup tested starting from -40 °C nominal voltage
● during transport	-40 ... +85 °C
● during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	screw terminal
● at input	L, N, PE: 1 screw terminal each for 0.2 ... 4 mm² single-core/finely stranded
● at output	+, -: 2 screw terminals each for 0.2 ... 4 mm²
● for auxiliary contacts	13, 14 (alarm signal), 15, 16 (Remote ON OFF): 1 screw terminal each for 0.14 ... 1.5 mm²
mechanical data	
width × height × depth of the enclosure	90 × 125 × 125 mm
installation width × mounting height	90 mm × 225 mm
required spacing	
● top	50 mm
● bottom	50 mm
● left	0 mm
● right	0 mm

© Copyright Siemens
Downloaded from Arrow.com.

fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
● DIN-rail mounting	Yes
● S7 rail mounting	No
● wall mounting	No
housing can be lined up	Yes
net weight	1.2 kg
accessories	
electrical accessories	Buffer module
mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20
further information internet links	
internet link	
● to website: Industry Mall	https://mall.industry.siemens.com
● to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
● to web page: power supplies	https://siemens.com/sitop
● to website: CAx-Download-Manager	https://siemens.com/cax
● to website: Industry Online Support	https://support.industry.siemens.com
additional information	
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)

Classifications

	Version	Classification
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

Approvals Certificates

Environmental Product Declaration	
● global warming potential [CO2 eq] / during manufacturing	28.7 kg
● global warming potential [CO2 eq] / during operation	785 kg
● global warming potential [CO2 eq] / after end of life	0.24 kg
● global warming potential [CO2 eq] / total	814.2 kg

Environment	General Product Approval

© Copyright Siemens
Downloaded from Arrow.com.

Manufacturer Declaration

Declaration of Conformity

General Product Approval					
China RoHS					BIS CRS

Maritime application	other
	Miscellaneous

last modified: 5/5/2026

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.