


LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED	26SEP2012	-	JE
			A1	EOL BY ECR-19-019907	02JAN2020	A.L	H.L







DETAIL M
SCALE 10:1

HOUSING
QTY: 1

CHICKLET
QTY: 15

- CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
- 0.76µm MIN MATTE TIN OVER 1.27µm MIN NICKEL
- MATERIAL:
CONTACT - COPPER ALLOY
SHIELD - PHOSPHER BRONZE
HOUSING AND CHICKLET - GLASS FILLED POLYESTER
- REFERENCE APPLIATION SPEC 114-13020 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS
- DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER
- SEATING HEIGHT TO BOARD SURFACE
- CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995
- DATE CODE
- PART NUMBER



RECOMMENDED PRINTED
CIRCUIT BOARD LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD
SCALE 4:1

5120948-1
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.J. MAGARO CHK R.A. PATTERSON APVD	14SEP2004 14SEP2004 -			TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, 6 ROW, 90 POSITION, VERTICAL, Z-PACK HS3	SIZE A	CAGE CODE 00779	DRAWING NO 5120948	RESTRICTED TO REV A1	
		0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ±0.050 4 PLC ± ANGLES ±1° FINISH SHIELD: 1 CONTACTS: 2							
MATERIAL		PRODUCT SPEC 108-1957 APPLICATION SPEC 114-13020 WEIGHT -							
		CUSTOMER DRAWING							
		SCALE		5:1	SHEET		1	OF	1

OBSELETE