
TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

WIRE-TO-BOARD CONNECTOR CONTACTS



✔ Active

TE CONNECTIVITY (TE)

MOD-2 SNAP-IN REC CONT. FORM

AMPMODU | AMPMODU IV/V

172788-1
TE Internal Number: 172788-1

EU RoHS Compliant
EU ELV Compliant

Contact Type Socket

Wire/Cable Size (AWG) 26 – 22

Wire/Cable Size (mm^2) .12 – .4

Contact Mating Area Plating Material Gold

Packaging Method Strip

PRODUCT DRAWING
Japanese

3D PDF

DOCUMENTATION

Product Drawings

REC CONTACT, AMPMMODU MOD II CRIMP ON SNAP IN

PDF **(TIFF AVAILABLE)**

Japanese

CAD Files

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Downloaded from Arrow.com.

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

English

Product Specifications

Application Specification

CRIMPING AMPMODU MOD II, RECEPTACLE CONTACT

TIF

English

CRIMPING AMPMODU MOD II, RECEPTACLE CONTACT

TIF

Japanese

CRIMPING AMPMODU MOD II, RECEPTACLE CONTACT

PDF

English

CRIMPING AMPMODU MOD II, RECEPTACLE CONTACT

PDF

Japanese

Product Specification

AMP MODU MOD II , HOUSING LOCK CONNECTOR

PDF

English

AMP MODU MOD II , HOUSING LOCK CONNECTOR

TIF

English

Qualification Test Report

AMPMODU Mod II Housing Lock Connector

PDF

English

AMPMODU Mod II Housing Lock Connector

TIF

English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector & Contact Terminates To Wire & Cable
Wire/Cable Type Discrete Wire
Product Type Contact
Applied Pressure Standard
With Insulation Support Yes

Downloaded from Arrow.com.

Electrical Characteristics

Insulation Resistance (MΩ) 5000
Operating Voltage (VAC) 50

Contact Features

Contact Type Socket
Contact Mating Area Plating Material Gold
Contact Base Material Phosphor Bronze
Contact Mating Area Plating Thickness (µin) 15

Termination Features

Termination Method to Wire/Cable Crimp

Dimensions

Wire/Cable Size (AWG) 26 – 22
Wire/Cable Size (mm²) .12 – .4
Insulation Diameter .89 – 1.55 mm [.035 – .061 in]

Usage Conditions

Operating Temperature Range (°C) -40 – 85

Packaging Features

Packaging Method Strip
Packaging Quantity 10000

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.