



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.65 mm²**

Mating Tab Width: **4.75 mm [.187 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Electrical Characteristics

Voltage Rating	250 V
----------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp



Barrel Type	Open
-------------	------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Locking Lance Height	1.2 mm
Wire Insulation Support	With
Mating Retention Type	Locking Lance
Extraction Force	4 Newton

Dimensions

Product Length	16 mm[.629 in]
Compatible Insulation Diameter Range	2.31 – 3.3 mm[.091 – .129 in]
Terminal Material Thickness	.25 mm[.01 in]
Wire Size	.51 – 1.65 mm ²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	8000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



KIT

REPRESENTATION ONLY

TE Part # 7-2150309-7
[OCEAN_2.0_SPARE_PART_KIT-090F130F](#)



TE Part # 2150309-1
[OCEAN_2.0_APPLICATOR-E-090F130F-REM](#)



TE Part # 2150309-2
[OCEAN_2.0_APPLICATOR-E-090F130F-REA](#)




TE Part # 281197-5
[FF 187 REC 1.0-2.5MM2 PTBR \(RE REELING\)](#)



TE Part # 281197-6
[FF 187 REC 1.0-2.5MM2 PTBR](#)

Also in the Series | FASTIN-FASTON 187



[Crimp Terminal Housings\(5\)](#)




[Insertion & Extraction Tools\(1\)](#)




[Quick Disconnects\(20\)](#)

Customers Also Bought



TE Part #103735-6
07 MTE HDR SRST LATCH .100CL




TE Part #170089-1
FF 250 REC 14-12AWG BR



TE Part #208488-1
CMC PLUG ASSEMBLY,SZ 22




TE Part #1-641215-0
10P MTA100 HDR ASSY FL/ST 30AU




TE Part #6-1419166-1
1X4MALE IL ASSY "A"



TE Part #5-1546686-3
6PCV-05-1396=0.375" 6 Series Tri-Barrier



TE Part #9-1617748-2
FCA-210-0919M=M83536/9-019M



TE Part #1617754
FCA-410-1517M=M83536/15-017M



TE Part #2-1617799-5
FCAC-325-BZ4=RELAY



TE Part #1-1904045-6
V23333Z0001B046-EV-100

Documents

Product Drawings

FF 187 REC 0.5-1.5MM2 TPPB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_280919-4_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_280919-4_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_280919-4_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

FASTIN-FASTON Connector, .187 rec. etc.