


NAiS

ULTRA SMALL 2 AMP.
POLARIZED RELAY WITH
2,500 V SURGE VOLTAGE

TW-RELAYS



UL File No.: E43149

CSA File No.: LR26550

- Surge withstand between contacts and coil: 2,500 V (Bellcore rating)
- Current surge interrupt: 4.2 A 700 V AC
- High contact capacity: 2 A 30 V DC

SPECIFICATIONS

Contact

| | | |
|--|---|--------------------|
| Arrangement | 2 Form C | |
| Initial contact resistance, max. (By voltage drop 6 V DC 1 A) | 60 mΩ | |
| Contact material | Gold-clad silver nickel | |
| Rating (resistive load) | Max. switching power | 60 W, 62.5 VA |
| | Max. switching voltage | 220 V DC, 250 V AC |
| | Max. switching current | 2 A |
| UL/CSA rating | 2 A 30 V DC 0.5 A 125 V AC 0.3 A 110 V DC | |
| Expected life (min. oper- tions) | Mechanical (at 180 cpm) | |
| | 2 A 30 V DC resistive | 10 ⁸ |
| | 1 A 30 V DC resistive | 10 ⁵ |
| | 0.5 A 125 V AC resistive | 5×10 ⁵ |

Characteristics (at 20°C 68°F)

| | | |
|--|---|---|
| Max. operating speed (at rated load) | 20 cpm | |
| Operate time* (at nominal voltage) | Max. 4 msec. (Approx. 2 msec.) | |
| Release time* (at nominal voltage) | Max. 4 msec. (Approx. 1 msec.) | |
| Set time* (latching) (at nominal voltage) | Max. 4 msec. (Approx. 2 msec.) | |
| Reset time* (latching) (at nominal voltage) | Max. 4 msec. (Approx. 2 msec.) | |
| Initial break- down voltage | Between open contacts | 1,000 Vrms for 1 min. |
| | Between contact sets | 1,000 Vrms for 1 min. |
| | Between contact and coil | 1,800 Vrms for 1 min. |
| Surge voltage | Between open contacts (10×160 μsec.) | 1,500 V FCC |
| | Between contacts and coil (2×10 μsec.) | 2,500 V |
| Current surge capacity (See Note) | | 4.2 A 700 V AC |
| Initial insulation resistance | | Min. 1,000 MΩ (at 500 V DC) |
| Temperature rise (at nominal voltage) | | Max. 50°C |
| Ambient temperature** | | -40°C to +85°C -40°F to +185°F (Not freezing and condensing at low temperature) |
| Shock resistance | Functional | Min. 735 m/s ² (75 G) |
| | Destructive | Min. 980 m/s ² (100 G) |
| Vibration resistance | Functional | 196 m/s ² (20 G), 10 to 55 Hz at double amplitude of 3.3 mm |
| | Destructive | 294 m/s ² (30 G), 10 to 55 Hz at double amplitude of 5 mm |
| Unit weight | | Approx. 2 g .071 oz |

*Excluding contact bounce time

**The maximum ambient temperature allows for coil temperature rise at maximum allowable coil voltage.

As for the applicable range of continuous carrying current against ambient temperature, please refer to „Maximum value of continuous carrying current“ chart. (Page 3-38)

Note: The contacts can interrupt a 4.2 A 700 V AC load four times, with 2 interruptions within the positive phase angle, and 2 interruptions within the negative phase angles of a sine wave form.

ORDERING INFORMATION

Ex. TW **2** — **L2** — **H** — **12V**

| Contact arrangement | Operating function | Terminal shape | Coil voltage (DC) |
|---------------------|--|---|-----------------------------------|
| 2: 2 Form C | Nil: Single side stable L: 1 coil latching L2: 2 coil latching | Nil: Standard PC board terminal H: Self-clinching terminal | 3, 4.5, 5, 6, 9, 12, 24, 48* V |

*48 V coil type: Single side stable only

TYPES AND COIL DATA (at 20°C 68°F)

| Operating function | Part No. | | Nominal voltage, V DC | Pick-up voltage, V DC (max.) | Drop-out voltage, V DC (min.) | Nominal operating current, mA ($\pm 10\%$) | Coil resistance, Ω ($\pm 10\%$) | Nominal operating power, mW | Max. allowable voltage, V DC |
|--------------------|----------------------------|-------------------------|-----------------------|------------------------------|-------------------------------|--|--|-----------------------------|------------------------------|
| | Standard PC board terminal | Self-clinching terminal | | | | | | | |
| Single side stable | TW2-3V | TW2-H-3V | 3 | 2.25 | 0.3 | 46.7 | 64.3 | 140 | 4.5 |
| | TW2-4.5V | TW2-H-4.5V | 4.5 | 3.38 | 0.45 | 31.1 | 145 | 140 | 6.7 |
| | TW2-5V | TW2-H-5V | 5 | 3.75 | 0.5 | 28.1 | 178 | 140 | 7.5 |
| | TW2-6V | TW2-H-6V | 6 | 4.5 | 0.6 | 23.3 | 257 | 140 | 9 |
| | TW2-9V | TW2-H-9V | 9 | 6.75 | 0.9 | 15.5 | 579 | 140 | 13.5 |
| | TW2-12V | TW2-H-12V | 12 | 9 | 1.2 | 11.7 | 1,028 | 140 | 18 |
| | TW2-24V | TW2-H-24V | 24 | 18 | 2.4 | 8.3 | 2,880 | 200 | 36 |
| | TW2-48V | TW2-H-48V | 48 | 36 | 4.8 | 5.42 | 8,860 | 260 | 57.6 |

| Operating function | Part No. | | Nominal voltage, V DC | Set voltage, V DC (max.) | Reset voltage, V DC (max.) | Nominal operating current, mA ($\pm 10\%$) | Coil resistance, Ω ($\pm 10\%$) | Nominal operating power, mW | Max. allowable voltage, V DC |
|--------------------|----------------------------|-------------------------|-----------------------|--------------------------|----------------------------|--|--|-----------------------------|------------------------------|
| | Standard PC board terminal | Self-clinching terminal | | | | | | | |
| 1 coil latching | TW2-L-3V | TW2-L-H-3V | 3 | 2.25 | 2.25 | 33.3 | 90 | 100 | 4.5 |
| | TW2-L-4.5V | TW2-L-H-4.5V | 4.5 | 3.38 | 3.38 | 22.2 | 202.5 | 100 | 6.7 |
| | TW2-L-5V | TW2-L-H-5V | 5 | 3.75 | 3.75 | 20 | 250 | 100 | 7.5 |
| | TW2-L-6V | TW2-L-H-6V | 6 | 4.5 | 4.5 | 16.7 | 360 | 100 | 9 |
| | TW2-L-9V | TW2-L-H-9V | 9 | 6.75 | 6.75 | 11.1 | 810 | 100 | 13.5 |
| | TW2-L-12V | TW2-L-H-12V | 12 | 9 | 9 | 8.3 | 1,440 | 100 | 18 |
| | TW2-L-24V | TW2-L-H-24V | 24 | 18 | 18 | 4.17 | 5,760 | 100 | 36 |
| 2 coil latching | TW2-L2-3V | TW2-L2-H-3V | 3 | 2.25 | 2.25 | 66.7 | 45 | 200 | 4.5 |
| | TW2-L2-4.5V | TW2-L2-H-4.5V | 4.5 | 3.38 | 3.38 | 44.5 | 101.2 | 200 | 6.7 |
| | TW2-L2-5V | TW2-L2-H-5V | 5 | 3.75 | 3.75 | 40 | 125 | 200 | 7.5 |
| | TW2-L2-6V | TW2-L2-H-6V | 6 | 4.5 | 4.5 | 33.3 | 180 | 200 | 9 |
| | TW2-L2-9V | TW2-L2-H-9V | 9 | 6.75 | 6.75 | 22.2 | 405 | 200 | 13.5 |
| | TW2-L2-12V | TW2-L2-H-12V | 12 | 9 | 9 | 16.7 | 720 | 200 | 18 |
| | TW2-L2-24V | TW2-L2-H-24V | 24 | 18 | 18 | 8.3 | 2,880 | 200 | 28.8 |


Notes: 1. Specified value of the pick-up, drop-out, set and reset voltage is with the condition of square wave coil pulse.

2. Standard packing: Tube: 50 pcs.; Case: 1,000 pcs.


3. In case of 5 V drive circuit, it is recommended to use 4.5 V type relay.

DIMENSIONS


mm inch



Standard PC board terminal




Self-clinching terminal

General tolerance: $\pm 0.3 \pm .012$

PC board pattern (Copper-side view)

- Single side stable
- 1 coil latching
- 2 coil latching


Tolerance: $\pm 0.1 \pm .004$

Schematic (Bottom view)

- Single side stable
(Deenergized condition)



- 2 coil latching
(Reset condition)



- 1 coil latching
(Reset condition)



- 2 coil latching
(Reset condition)

*Orientation stripe
located on top of relay.


DATA

1. Maximum value of continuous carrying current

Test conditions:


Coil applied voltage: 110% of rated voltage

Continuous carrying current: 1,000 hours




4. Mechanical life

Tested sample: TW2-12V, 10 pcs.




5-(2). Electrical life


Tested sample: TW2-12V, 6 pcs.

Condition: 0.5 A 125 V AC resistive load, 20 cpm
Change of pick-up and drop-out voltage

2. Maximum switching power





3. Life curve




5-(1). Electrical life

Tested sample: TW2-12V, 6 pcs.

Condition: 2 A 30 V DC resistive load, 20 cpm
Change of contact resistance


5-(2). Electrical life

Tested sample: TW2-12V, 6 pcs.

Condition: 0.5 A 125 V AC resistive load, 20 cpm
Change of contact resistance


6. Coil temperature rise

Tested sample: TW2-xxV
Point measured: Inside the coil
Ambient temperature: 22°C 72°F




9. Distribution of pick-up and drop-out voltage

Tested sample: TW2-12V, 50 pcs.




12. Distribution of contact resistance

Tested sample: TW2-12V, 30 pcs.




13-(3). High frequency characteristics

Tested sample: TW2-xxV
V.S.W.R.





7. Operate and release time

Tested sample: TW2-12V, 5 pcs.




10. Distribution of set and reset voltage

Tested sample: TW2-L-12V, 50 pcs.


13-(1). High-frequency characteristic
Isolation characteristics

14-(1). Malfunction shock (single side stable)





8. Set and reset time

Tested sample: TW2-L-12V, 5 pcs.



11. Ambient temperature characteristics

Tested sample: TW2-12V, 5 pcs.

13-(2). High frequency characteristics
Insertion loss characteristics

14-(2). Malfunction shock (latching)

