

Housing - HC-STA-D07-BWSCM-EL-AL - 1419250


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Panel mounting base D7, With single locking latch, Material: Die-cast aluminum, salt water resistant, Protective cover material: PA, Height: 25.5 mm, Cable gland: none, Gland: no, Protective cover: Yes, Standard, for pin inserts



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 159812
GTIN	4055626159812
Weight per Piece (excluding packing)	20.000 g
Custom tariff number	85389099
Country of origin	China

Technical data

Dimensions

Height	25.5 mm
Width	34.2 mm
Length	24.2 mm
Length of the assembly cutout	21.5 mm
Width of the assembly cutout	21.5 mm

Ambient conditions

Degree of protection of housing (IP)	IP66
	IP67
Degree of protection of housing (NEMA)	4 (UL 50e)

Housing - HC-STA-D07-BWSCM-EL-AL - 1419250

Technical data

Ambient conditions


	4X (UL 50e)
	12 (UL 50e)
Ambient temperature (operation)	-40 °C ... 125 °C

General


Note	for contact inserts HC-A03, A04, D07, D08, Q02, Q03, Q04, Q05, Q07, Q12
Size	D7
Housing type	Panel mounting base
Locking type	With single locking latch
Screw connection	none
Protective cover	Yes
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	Uncoated
Seal material	NBR
Material, protective cover	PA
Assembly instructions	For mounting pin inserts

Drawings

Dimensional drawing



Dimensional drawing



Panel cutout

Approvals

Approvals

Approvals

EAC

Housing - HC-STA-D07-BWSCM-EL-AL - 1419250

Approvals

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	---	---------------