

DDR4 SDRAM RDIMM

Addendum

MTA36ASF8G72PZ – 64GB


Introduction

Information provided here is in addition to or supercedes information provided in the Micron DDR4 RDIMM Core data sheet.

Features

- DDR4 functionality and operations supported as defined in the component data sheet
- Features and specifications supported in the Micron DDR4 RDIMM Core data sheet
- 288-pin, registered dual in-line memory module (RDIMM)
- Fast data transfer rates: PC4-3200, PC4-2933
- 64GB (8 Gig x 72)
- Dual-rank
- 16 internal banks; 4 groups of 4 banks each

Figure 1: 288-Pin RDIMM (MO-309, R/C-B3)



Options

- Operating temperature
 - Commercial ($0^{\circ}\text{C} \leq T_{\text{OPER}} \leq 95^{\circ}\text{C}$)
- Package
 - 288-pin DIMM (halogen-free)
- Frequency/CAS latency
 - 0.625ns @ CL = 22 (DDR4-3200)
 - 0.682ns @ CL = 21 (DDR4-2933)

Marking

None
Z
-3G2
-2G9

Table 1: Addressing

Parameter	64GB
Row address	256K A[17:0]
Column address	1K A[9:0]
Device bank group address	4 BG[1:0]
Device bank address per group	4 BA[1:0]
Device configuration	16Gb (4 Gig x 4), 16 banks
Module rank address	2 CS_n[1:0]

Table 2: Part Numbers and Timing Parameters – 64GB Modules

Base device: MT40A4G4,¹ 16Gb DDR4 SDRAM

Part Number ²	Module Density	Configuration	Module Bandwidth	Memory Clock/ Data Rate	Clock Cycles (CL-nRCD-nRP)
MTA36ASF8G72PZ-3G2__	64GB	8 Gig x 72	25.6 GB/s	0.625ns/3200 MT/s	22-22-22
MTA36ASF8G72PZ-2G9__	64GB	8 Gig x 72	23.47 GB/s	0.682ns/2933 MT/s	21-21-21

- Notes:
1. The data sheet for the base device can be found on micron.com.
 2. All part numbers end with a two-place code (not shown) that designates component and PCB revisions. Consult factory for current revision codes. Example: MTA36ASF8G72PZ-3G2B2.

Important Notes and Warnings

Micron Technology, Inc. ("Micron") reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions. This document supersedes and replaces all information supplied prior to the publication hereof. You may not rely on any information set forth in this document if you obtain the product described herein from any unauthorized distributor or other source not authorized by Micron.

Automotive Applications. Products are not designed or intended for use in automotive applications unless specifically designated by Micron as automotive-grade by their respective data sheets. Distributor and customer/distributor shall assume the sole risk and liability for and shall indemnify and hold Micron harmless against all claims, costs, damages, and expenses and reasonable attorneys' fees arising out of, directly or indirectly, any claim of product liability, personal injury, death, or property damage resulting directly or indirectly from any use of non-automotive-grade products in automotive applications. Customer/distributor shall ensure that the terms and conditions of sale between customer/distributor and any customer of distributor/customer (1) state that Micron products are not designed or intended for use in automotive applications unless specifically designated by Micron as automotive-grade by their respective data sheets and (2) require such customer of distributor/customer to indemnify and hold Micron harmless against all claims, costs, damages, and expenses and reasonable attorneys' fees arising out of, directly or indirectly, any claim of product liability, personal injury, death, or property damage resulting from any use of non-automotive-grade products in automotive applications.

Critical Applications. Products are not authorized for use in applications in which failure of the Micron component could result, directly or indirectly in death, personal injury, or severe property or environmental damage ("Critical Applications"). Customer must protect against death, personal injury, and severe property and environmental damage by incorporating safety design measures into customer's applications to ensure that failure of the Micron component will not result in such harms. Should customer or distributor purchase, use, or sell any Micron component for any critical application, customer and distributor shall indemnify and hold harmless Micron and its subsidiaries, subcontractors, and affiliates and the directors, officers, and employees of each against all claims, costs, damages, and expenses and reasonable attorneys' fees arising out of, directly or indirectly, any claim of product liability, personal injury, or death arising in any way out of such critical application, whether or not Micron or its subsidiaries, subcontractors, or affiliates were negligent in the design, manufacture, or warning of the Micron product.

Customer Responsibility. Customers are responsible for the design, manufacture, and operation of their systems, applications, and products using Micron products. ALL SEMICONDUCTOR PRODUCTS HAVE INHERENT FAILURE RATES AND LIMITED USEFUL LIVES. IT IS THE CUSTOMER'S SOLE RESPONSIBILITY TO DETERMINE WHETHER THE MICRON PRODUCT IS SUITABLE AND FIT FOR THE CUSTOMER'S SYSTEM, APPLICATION, OR PRODUCT. Customers must ensure that adequate design, manufacturing, and operating safeguards are included in customer's applications and products to eliminate the risk that personal injury, death, or severe property or environmental damages will result from failure of any semiconductor component.

Limited Warranty. In no event shall Micron be liable for any indirect, incidental, punitive, special or consequential damages (including without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort, warranty, breach of contract or other legal theory, unless explicitly stated in a written agreement executed by Micron's duly authorized representative.

DQ Map

Table 3: Component-to-Module DQ Map Front (R/C-B3)

Component Reference Number	Component DQ	Module DQ	Module Pin Number	Component Reference Number	Component DQ	Module DQ	Module Pin Number
U2	0	7	155	U3	0	15	166
	1	5	148		1	13	159
	2	6	10		2	14	21
	3	4	3		3	12	14
U4	0	23	177	U5	0	31	188
	1	21	170		1	29	181
	2	22	32		2	30	43
	3	20	25		3	28	36
U6	0	CB7	199	U8	0	39	247
	1	CB5	192		1	37	240
	2	CB6	54		2	38	102
	3	CB4	47		3	36	95
U9	0	47	258	U10	0	55	269
	1	45	251		1	53	262
	2	46	113		2	54	124
	3	44	106		3	52	117
U11	0	63	280	U12	0	3	157
	1	61	273		1	1	150
	2	62	135		2	2	12
	3	60	128		3	0	5
U13	0	10	23	U14	0	16	27
	1	9	161		1	18	34
	2	11	168		2	17	172
	3	8	16		3	19	179
U15	0	24	38	U16	0	CB0	49
	1	26	45		1	CB2	56
	2	25	183		2	CB1	194
	3	27	190		3	CB3	201
U17	0	32	97	U18	0	41	253
	1	34	104		1	42	115
	2	33	242		2	40	108
	3	35	249		3	43	260

Table 3: Component-to-Module DQ Map Front (R/C-B3) (Continued)

Component Reference Number	Component DQ	Module DQ	Module Pin Number	Component Reference Number	Component DQ	Module DQ	Module Pin Number
U19	0	51	271	U20	0	59	282
	1	49	264		1	57	275
	2	50	126		2	58	137
	3	48	119		3	56	130

Table 4: Component-to-Module DQ Map Back (R/C-B3)

Component Reference Number	Component DQ	Module DQ	Module Pin Number	Component Reference Number	Component DQ	Module DQ	Module Pin Number
U21	0	61	273	U22	0	53	262
	1	63	280		1	55	269
	2	60	128		2	52	117
	3	62	135		3	54	124
U23	0	45	251	U24	0	37	240
	1	47	258		1	39	247
	2	44	106		2	36	95
	3	46	113		3	38	102
U25	0	CB5	192	U26	0	29	181
	1	CB7	199		1	31	188
	2	CB4	47		2	28	36
	3	CB6	54		3	30	43
U27	0	21	170	U28	0	13	159
	1	23	177		1	15	166
	2	20	25		2	12	14
	3	22	32		3	14	21
U29	0	5	148	U30	0	57	275
	1	7	155		1	59	282
	2	4	3		2	56	130
	3	6	10		3	58	137
U31	0	49	264	U32	0	42	115
	1	51	271		1	41	253
	2	48	119		2	43	260
	3	50	126		3	40	108

Table 4: Component-to-Module DQ Map Back (R/C-B3) (Continued)

Component Reference Number	Component DQ	Module DQ	Module Pin Number	Component Reference Number	Component DQ	Module DQ	Module Pin Number
U33	0	34	104	U34	0	CB2	56
	1	32	97		1	CB0	49
	2	35	249		2	CB3	201
	3	33	242		3	CB1	194
U35	0	26	45	U36	0	18	34
	1	24	38		1	16	27
	2	27	190		2	19	179
	3	25	183		3	17	172
U37	0	9	161	U38	0	1	150
	1	10	23		1	3	157
	2	8	16		2	0	5
	3	11	168		3	2	12

I_{DD} Specifications

Table 5: DDR4 I_{DD} Specifications and Conditions (0° ≤ T_C ≤ 85°) – 64GB (Die Revision E)

Values are for the MT40A4G4 DDR4 SDRAM only and are computed from values specified in the 16Gb (4 Gig x 4) component data sheet

Parameter	Symbol	3200	2933	Units
One bank ACTIVATE-PRECHARGE current	I _{DD0} ¹	1674	1656	mA
One bank ACTIVATE-PRECHARGE, wordline boost, I _{pp} current	I _{PP0} ¹	90	90	mA
One bank ACTIVATE-READ-PRECHARGE current	I _{DD1} ¹	1872	1854	mA
Precharge standby current	I _{DD2N} ²	1620	1584	mA
Precharge standby ODT current	I _{DD2NT} ¹	1602	1584	mA
Precharge power-down current	I _{DD2P} ²	1368	1368	mA
Precharge quiet standby current	I _{DD2Q} ²	1512	1512	mA
Active standby current	I _{DD3N} ²	2160	2124	mA
Active standby I _{pp} current	I _{PP3N} ²	72	72	mA
Active power-down current	I _{DD3P} ²	1728	1692	mA
Burst read current	I _{DD4R} ¹	2970	2826	mA
Burst write current	I _{DD4W} ¹	2574	2502	mA
Different logic rank burst refresh current (1x REF)	I _{DD5R} ¹	1908	1908	mA
Different logic rank burst refresh I _{pp} current (1x REF)	I _{PP5R} ¹	108	108	mA
Self refresh current: Normal temperature range (0°C to 85°C)	I _{DD6N} (0–85°C) ²	1908	1908	mA
Self refresh current: Extended temperature range (0°C to 95°C)	I _{DD6E} (0–95°C) ²	4068	4068	mA
Self refresh current: Reduced temperature range (0°C to 45°C)	I _{DD6R} (0–45°C) ²	720	720	mA
Auto self refresh current (25°C)	I _{DD6A} (25°C) ²	396	396	mA
Auto self refresh current (45°C)	I _{DD6A} (45°C) ²	720	720	mA
Auto self refresh current (75°C)	I _{DD6A} (75°C) ²	1836	1836	mA
Auto self refresh current (95°C)	I _{DD6A} (95°C) ²	4068	4068	mA
Auto self refresh I _{pp} current (0°C to 95°C)	I _{PP6X} ²	216	216	mA
Bank interleaved read current	I _{DD7} ¹	4230	4194	mA
Bank interleaved read I _{pp} current	I _{PP7} ¹	324	324	mA
Maximum power-down current	I _{DD8} ²	1296	1296	mA

- Notes:
1. One module rank in the active I_{DD}/I_{pp}, the other rank in I_{DD2P}/I_{PP3N}.
 2. All ranks in this I_{DD}/I_{pp} condition.
 3. When T_C > 85°C, the I_{DD} and I_{pp} values must be derated. Refer to the base device data sheet I_{DD} and I_{pp} specification tables for derating values for the applicable die-revision.

Table 6: DDR4 I_{DD} Specifications and Conditions (0° ≤ T_C ≤ 85°) – 64GB (Die Revision B)


Values are for the MT40A4G4 DDR4 SDRAM only and are computed from values specified in the 16Gb (4 Gig x 4) component data sheet

Parameter	Symbol	3200	2933	Units
One bank ACTIVATE-PRECHARGE current	I _{DD0} ¹	1854	1836	mA
One bank ACTIVATE-PRECHARGE, wordline boost, I _{PP} current	I _{PP0} ¹	126	126	mA
One bank ACTIVATE-READ-PRECHARGE current	I _{DD1} ¹	2034	2016	mA
Precharge standby current	I _{DD2N} ²	1872	1836	mA
Precharge standby ODT current	I _{DD2NT} ¹	1782	1764	mA
Precharge power-down current	I _{DD2P} ²	1548	1548	mA
Precharge quiet standby current	I _{DD2Q} ²	1692	1692	mA
Active standby current	I _{DD3N} ²	2808	2772	mA
Active standby I _{PP} current	I _{PP3N} ²	108	108	mA
Active power-down current	I _{DD3P} ²	2484	2448	mA
Burst read current	I _{DD4R} ¹	3870	3726	mA
Burst write current	I _{DD4W} ¹	3726	3600	mA
Different logic rank burst refresh current (1x REF)	I _{DD5R} ¹	2196	2178	mA
Different logic rank burst refresh I _{PP} current (1x REF)	I _{PP5R} ¹	144	144	mA
Self refresh current: Normal temperature range (0°C to 85°C)	I _{DD6N} (0–85°C) ²	2412	2412	mA
Self refresh current: Extended temperature range (0°C to 95°C)	I _{DD6E} (0–95°C) ²	4356	4356	mA
Self refresh current: Reduced temperature range (0°C to 45°C)	I _{DD6R} (0–45°C) ²	1044	1044	mA
Auto self refresh current (25°C)	I _{DD6A} (25°C) ²	360	360	mA
Auto self refresh current (45°C)	I _{DD6A} (45°C) ²	1044	1044	mA
Auto self refresh current (75°C)	I _{DD6A} (75°C) ²	2196	2196	mA
Auto self refresh current (95°C)	I _{DD6A} (95°C) ²	4356	4356	mA
Auto self refresh I _{PP} current (0°C to 95°C)	I _{PP6X} ²	396	396	mA
Bank interleave read current	I _{DD7} ¹	5058	4932	mA
Bank interleave read I _{PP} current	I _{PP7} ¹	252	252	mA
Maximum power-down current	I _{DD8} ²	1440	1440	mA

- Notes:
1. One module rank in the active I_{DD}/I_{PP}, the other rank in I_{DD2P}/I_{PP3N}.
 2. All ranks in this I_{DD}/I_{PP} condition.
 3. When T_C > 85°C, the I_{DD} and I_{PP} values must be derated. Refer to the base device data sheet I_{DD} and I_{PP} specification tables for derating values for the applicable die-revision.

Functional Block Diagram

Figure 2: Functional Block Diagram, R/C-B3



Note: 1. The ZQ ball on each DDR4 component is connected to an external $240\Omega \pm 1\%$ resistor that is tied to ground. It is used for the calibration of the component's ODT and output driver.



64GB (x72, ECC, DR) 288-Pin DDR4 RDIMM Functional Block Diagram

8000 S. Federal Way, P.O. Box 6, Boise, ID 83707-0006, Tel: 208-368-4000

www.micron.com/products/support Sales inquiries: 800-932-4992

Micron and the Micron logo are trademarks of Micron Technology, Inc.

All other trademarks are the property of their respective owners.

This data sheet contains minimum and maximum limits specified over the power supply and temperature range set forth herein. Although considered final, these specifications are subject to change, as further product development and data characterization sometimes occur.