


827914-3 Product Details



827914-3

TE Part Number: 827914-3

Active

Add to Part List

Post Shunts

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Shunt Type = Mod. IV
- Number of Positions = 2
- 2.54 mm Centerline
- Tin (100) Contact Mating Area Plating Material
- Shunt Style = Open Top

[View all Features](#) | [Find Similar Products](#)

Live Product Chat

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product
- Request Samples

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [AMP Novo Shunt Connector](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Shunt Type = Mod. IV
- [Number of Positions](#) = 2
- [Shunt Style](#) = Open Top
- CSA Certified = Yes
- Comment = Loose piece of 142270-3

Termination Related Features:

- Height (mm [in]) = 6.00 [0.236]

Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]
- Handle = Without
- UL Rating = Recognized

Contact Related Features:

- Contact Mating Area Plating Material = Tin (100)
- Contact Material = Beryllium Copper

Housing Related Features:

- Housing Color = Black
- Housing Material = Polyester GF
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = Loose Piece

Other:

- Brand = AMP

Provide Website Feedback | Need Help?