

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.



Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

1.6 GHz SILICON MMIC DIFFERENTIAL WIDE BAND AMPLIFIER

DESCRIPTION

The μPC2726T is a silicon microwave monolithic integrated circuit designed for miniature differential amplifier. This IC operates up to 1.6 GHz and therefore is suitable for BS tuner, mobile communication and measurement equipment applications. This IC can also use as differential oscillator application.

This IC is manufactured using NEC's 20 GHz fr NESAT™ III silicon bipolar process. This process uses silicon nitride passivation film and gold electrodes. These materials can protect the chip surface from external pollution and prevent corrosion/migration. Thus, this IC has excellent performance, uniformity and reliability.

★ FEATURES

- Supply voltage : $V_{CC} = 4.5$ to 5.5 V
- Circuit current : $I_{CC} = 11.5$ mA TYP. @ $V_{CC} = 5.0$ V
- Power gain : $G_P = 15.0$ dB TYP. @ $f = 400$ MHz
- Saturated output power gain : $P_{O(sat)} = -2.0$ dBm @ $f = 400$ MHz
- High isolation : $ISL = 60$ dB TYP. @ $f = 400$ MHz
- Upper limit operating frequency : $f_u = 1.6$ GHz TYP. @ 3 dB down below from gain at $f = 400$ MHz

ORDERING INFORMATION

Part Number	Package	Supplying Form
μPC2726T-E3	6-pin minimold	- Embossed tape 8 mm wide 1, 2, 3 pin face the perforation side of the tape - Qty 3 kpcs/reel


Remark To order evaluation samples, please contact your local NEC sales office.
Part number for sample order: μPC2726T

Caution Electro-static sensitive devices

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.
Not all devices/types available in every country. Please check with local NEC representative for availability and additional information.


EXAMPLE FOR SYSTEM APPLICATION

DBS tuner



Caution The insertion point is different due to the specifications of conjunct devices.

PIN CONNECTIONS



Pin No.	Pin Name
1	$\overline{\text{INPUT}}$
2	GND
3	OUTPUT
4	$\overline{\text{OUTPUT}}$
5	V _{CC}
6	INPUT



PIN EXPLANATION

Pin No.	Pin Name	Applied Voltage (V)	Pin Voltage (V) ^{Note}	Function and Applications	Internal Equivalent Circuit
1 6	<u>INPUT</u> INPUT	—	3.45	Signal input pin.	
2	GND	0	—	Ground pin. This pin should be connected to system ground with minimum inductance. Ground pattern on the board should be formed as wide as possible. All the ground pins must be connected together with wide ground pattern to decrease impedance difference.	
3 4	<u>OUTPUT</u> OUTPUT	—	3.76	Signal output pin.	
5	V _{cc}	4.5 to 5.5	—	Power supply pin. This pin should be externally equipped with bypass capacitor to minimize ground impedance.	

Note Pin voltage is measured at V_{cc} = 3.0 V

ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Conditions	Ratings	Unit
Supply Voltage	V_{CC}	$T_A = +25^\circ\text{C}$	6	V
Power Dissipation	P_D	$T_A = +85^\circ\text{C}$ Note	280	mW
Operating Ambient Temperature	T_A		-40 to +85	$^\circ\text{C}$
Storage Temperature	T_{stg}		-55 to +150	$^\circ\text{C}$
Input Power	P_{in}	$T_A = +25^\circ\text{C}$	0	dBm

Note Mounted on double-sided copper clad $50 \times 50 \times 1.6$ mm epoxy grass PWB

RECOMMENDED OPERATING RANGE

Parameter	Symbol	MIN.	TYP.	MAX.	Unit
Supply Voltage	V_{CC}	4.5	5.0	5.5	V
Operating Ambient Temperature	T_A	-40	+25	+85	$^\circ\text{C}$

ELECTRICAL CHARACTERISTICS

(Unless otherwise specified, $T_A = +25^\circ\text{C}$, $V_{CC} = 5.0$ V, $Z_s = Z_L = 50 \Omega$, at single input)


Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Circuit Current	I_{CC}	No signal	8.0	11.5	15.0	mA
Power Gain	G_P	$f = 400$ MHz	11.0	15.0	17.0	dB
Noise Figure	NF	$f = 400$ MHz	—	4.5	6.0	dB
Upper Limit Operating Frequency	f_u	3 dB down below from gain at $f = 0.4$ GHz	1.0	1.6	—	GHz
Isolation	ISL	$f = 400$ MHz	—	60	—	dB
Input Return Loss	RL_{in}	$f = 400$ MHz	—	2.0	—	dB
Output Return Loss	RL_{out}	$f = 400$ MHz	—	4.0	—	dB
Saturated Output Power	$P_{O(sat)}$	$f = 400$ MHz, $P_{in} = -10$ dBm	-5.0	-2.0	—	dBm

STANDARD CHARACTERISTICS FOR REFERENCE ($T_A = +25^\circ\text{C}$, $Z_S = Z_L = 50\ \Omega$, at single input)


Parameters	Symbol	Test Conditions	Reference Value	Unit
Circuit Current	I_{CC}	$V_{CC} = 2\text{ V}$, No input signal	2.5	mA
Power Gain	G_P	$V_{CC} = 2\text{ V}$, $f = 400\text{ MHz}$	4.5	dB
Noise Figure	NF	$V_{CC} = 2\text{ V}$, $f = 400\text{ MHz}$	5.1	dB
Upper Limit Operating Frequency	f_u	3 dB down below flat gain at 0.4 GHz	2.4	GHz
Isolation	ISL	$V_{CC} = 2\text{ V}$, $f = 400\text{ MHz}$	58	dB
Input Return Loss	RL_{in}	$V_{CC} = 2\text{ V}$, $f = 400\text{ MHz}$	1.0	dB
Output Return Loss	RL_{out}	$V_{CC} = 2\text{ V}$, $f = 400\text{ MHz}$	4.0	dB
Maximum Output Power	$P_{O(sat)}$	$V_{CC} = 2\text{ V}$, $f = 400\text{ MHz}$, $P_{in} = -10\text{ dBm}$	-14	dBm
3rd Order Intermodulation Distortion 1	IM_{31}	$V_{CC} = 2\text{ V}$, $P_{O(each)} = -25\text{ dBm}$, $f_1 = 400\text{ MHz}$, $f_2 = 402\text{ MHz}$	-29	dBc
3rd Order Intermodulation Distortion 2	IM_{32}	$V_{CC} = 5\text{ V}$, $P_{O(each)} = -25\text{ dBm}$, $f_1 = 400\text{ MHz}$, $f_2 = 402\text{ MHz}$	-45	dBc

★ TEST CIRCUITS

DC Parameters



AC Parameters



CAPACITORS FOR THE V_{CC}, INPUT AND OUTPUT PINS

1 000 pF capacitors are recommendable as bypass capacitor for V_{CC} pin and coupling capacitors for input/output pins.


Bypass capacitor for V_{CC} pin is intended to minimize V_{CC} pin's ground impedance. Therefore, stable bias can be supplied against V_{CC} fluctuation.

Coupling capacitors for input/output pins are intended to minimize RF serial impedance and cut DC.


To get a flat gain from 100 MHz up, 1 000 pF capacitors are assembled on the test circuit. [Actually, 1 000 pF capacitors give flat gain at least 10 MHz. In the case of under 10 MHz operation, increase the value of coupling capacitor such as 2 200 pF. Because the coupling capacitors are determined by the equation of $C = 1/(2 \pi f Z_s)$.]

TYPICAL CHARACTERISTICS (Unless otherwise specified, $T_A = +25^\circ\text{C}$)


CIRCUIT CURRENT vs. SUPPLY VOLTAGE




CIRCUIT CURRENT vs. OPERATING AMBIENT TEMPERATURE




NOISE FIGURE, POWER GAIN vs. FREQUENCY




POWER GAIN vs. FREQUENCY




ISOLATION vs. FREQUENCY




INPUT RETURN LOSS, OUTPUT RETURN LOSS vs. FREQUENCY




OUTPUT POWER vs. INPUT POWER




OUTPUT POWER vs. INPUT POWER




OUTPUT POWER vs. INPUT POWER




OUTPUT POWER vs. INPUT POWER



SATURATED OUTPUT POWER vs. FREQUENCY




3RD ORDER INTERMODULATION DISTORTION vs. OUTPUT POWER OF EACH TONE




Remark The graphs indicate nominal characteristics.

S-PARAMETERS ($V_{CC} = 5.0\text{ V}$)

S₁₁-FREQUENCY




S₂₂-FREQUENCY



★ PACKAGE DIMENSIONS

6-PIN MINIMOLD (UNIT: mm)



★ **NOTES ON CORRECT USE**

- (1) Observe precautions for handling because of electro-static sensitive devices.
- (2) Form a ground pattern as widely as possible to minimize ground impedance (to prevent undesired oscillation).
All the ground pins must be connected together with wide ground pattern to decrease impedance difference.
- (3) The bypass capacitor should be attached to V_{CC} line.
- (4) The DC cut capacitor must be each attached to input pin and output pin.

★ **RECOMMENDED SOLDERING CONDITIONS**


This product should be soldered under the following recommended conditions. For soldering methods and conditions other than those recommended below, contact your NEC sales representative.

Soldering Method	Soldering Conditions	Recommended Condition Symbol
Infrared Reflow	Package peak temperature: 235°C or below Time: 30 seconds or less (at 210°C) Count: 3, Exposure limit: None ^{Note}	IR35-00-3
VPS	Package peak temperature: 215°C or below Time: 40 seconds or less (at 200°C) Count: 3, Exposure limit: None ^{Note}	VP15-00-3
Wave Soldering	Soldering bath temperature: 260°C or below Time: 10 seconds or less Count: 1, Exposure limit: None ^{Note}	WS60-00-1
Partial Heating	Pin temperature: 300°C or below Time: 3 seconds or less (per side of device) Exposure limit: None ^{Note}	—

Note After opening the dry pack, keep it in a place below 25°C and 65% RH for the allowable storage period.

Caution Do not use different soldering methods together (except for partial heating).

For details of recommended soldering conditions for surface mounting, refer to information document **SEMICONDUCTOR DEVICE MOUNTING TECHNOLOGY MANUAL (C10535E)**.



ATTENTION

OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
SENSITIVE
DEVICES

NESAT (NEC Silicon Advanced Technology) is a trademark of NEC Corporation.

- The information in this document is current as of July, 2001. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC's data sheets or data books, etc., for the most up-to-date specifications of NEC semiconductor products. Not all products and/or types are available in every country. Please check with an NEC sales representative for availability and additional information.
- No part of this document may be copied or reproduced in any form or by any means without prior written consent of NEC. NEC assumes no responsibility for any errors that may appear in this document.
- NEC does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC semiconductor products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of customer's equipment shall be done under the full responsibility of customer. NEC assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC endeavours to enhance the quality, reliability and safety of NEC semiconductor products, customers agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize risks of damage to property or injury (including death) to persons arising from defects in NEC semiconductor products, customers must incorporate sufficient safety measures in their design, such as redundancy, fire-containment, and anti-failure features.
- NEC semiconductor products are classified into the following three quality grades:
"Standard", "Special" and "Specific". The "Specific" quality grade applies only to semiconductor products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of a semiconductor product depend on its quality grade, as indicated below. Customers must check the quality grade of each semiconductor product before using it in a particular application.
 - "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots
 - "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)
 - "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.

The quality grade of NEC semiconductor products is "Standard" unless otherwise expressly specified in NEC's data sheets or data books, etc. If customers wish to use NEC semiconductor products in applications not intended by NEC, they must contact an NEC sales representative in advance to determine NEC's willingness to support a given application.

(Note)

- (1) "NEC" as used in this statement means NEC Corporation and also includes its majority-owned subsidiaries.
- (2) "NEC semiconductor products" means any semiconductor product developed or manufactured by or for NEC (as defined above).