




**Part Number :** [353620350](#)  
**Series Number :** 35362  
**Status :** Active - Proprietary  
**Product Category :** PCB Headers and Receptacles



---

## Drawings

[353620350 sd.pdf](#)

[353620350 stp.zip](#)

[Symbol and Footprint \(Multi-Format\)](#)

## Specifications


[PK-35362-001-001.pdf](#)

[PS-35507-003-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active - Proprietary
Category	PCB Headers and Receptacles
Series	35362
Description	2.00mm Pitch Sherlock Wire-to-Board Header, Vertical, with Positive Lock, 3 Circuits, with Kinked PC Tails, Natural
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	Sherlock
UPC	822348259175

### Agency

CSA	LR19980
UL	E29179

### Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V

### Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No

Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	8.50mm
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.247/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.30mm
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

### Solder Process Data

Lead-Free Process Capability	N/A
Max-Temp	260

---

### Mates With / Use With

#### Mates with Part(s)

Description	Part Number
Sherlock Receptacle Housings	<u>35507</u>

#### Use with Part(s)

Description	Part Number
2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 30-24 AWG, Reel	<u>502128000</u>

---

This document was generated on Dec 18, 2025