


REV	DOCUMENT	CHANGED BY	CHECK
8	0038111	PK 20MAY08	ASD



RELEASE NO.	SR - 6158
REPLACES	

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH				DRAWN	VK	17OCT 07		Honeywell				
OPERATING FORCE — — — — 3-5 OZ		CONTACT ARRANGEMENT S P D T				TOLERANCES UNLESS NOTED:				CHECK	RJ	17OCT 07						
RELEASE FORCE— — — — — 1 OZ MIN		30 VOLTS DC RATING				NO PLACE X ±				THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH - BASIC				
		SEA LEVEL 50,000 FT				ONE PLACE .X ± 0.030												
DIFFERENTIAL TRAVEL— — — .004 MAX		INDUCTIVE		3 AMP 2.5 AMP		TWO PLACE .XX ± 0.015												
OVERTRAVEL — — — — — .005 MIN		RESISTIVE		5 AMP 5 AMP		THREE PLACE .XXX ± 0.005												
		MAXIMUM INRUSH 24 AMP				FOUR PLACE .XXXX ±				INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE	TYPE	DRAWING NAME		REV
APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4				THIRD ANGLE PROJECTION 								B	I	21SM1-T		8
	UL, CSA	5A, 250 VAC								BRAND L4								
										RASTER				SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1	