

MMSZxxxT1 Series, SZMMSZxxxT1G Series

Zener Voltage Regulators

500 mW SOD-123 Surface Mount

Three complete series of Zener diodes are offered in the convenient, surface mount plastic SOD-123 package. These devices provide a convenient alternative to the leadless 34-package style.

Features

- 500 mW Rating on FR-4 or FR-5 Board
- Wide Zener Reverse Voltage Range – 2.4 V to 56 V
- Package Designed for Optimal Automated Board Assembly
- Small Package Size for High Density Applications
- ESD Rating of Class 3 (>16 kV) per Human Body Model
- AEC-Q101 Qualified and PPAP Capable
- SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements
- Pb-Free Packages are Available

Mechanical Characteristics

CASE: Void-free, transfer-molded, thermosetting plastic case

FINISH: Corrosion resistant finish, easily Solderable

MAXIMUM CASE TEMPERATURE FOR SOLDERING PURPOSES:

260°C for 10 Seconds

POLARITY: Cathode indicated by polarity band

FLAMMABILITY RATING: UL 94 V-0

MAXIMUM RATINGS

Rating	Symbol	Max	Unit
Total Power Dissipation on FR-5 Board, (Note 1) @ $T_L = 75^\circ\text{C}$ Derated above 75°C	P_D	500 6.7	mW mW/°C
Thermal Resistance, Junction-to-Ambient (Note 2)	$R_{\theta JA}$	340	°C/W
Thermal Resistance, Junction-to-Lead (Note 2)	$R_{\theta JL}$	150	°C/W
Junction and Storage Temperature Range	T_J, T_{stg}	-55 to +150	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.



1. FR-5 = 3.5 X 1.5 inches.

2. Thermal Resistance measurement obtained via infrared Scan Method.



ON Semiconductor®

<http://onsemi.com>



**SOD-123
CASE 425
STYLE 1**

MARKING DIAGRAM



xx = Device Code

M = Date Code

■ = Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping [†]
MMSZxxxT1	SOD-123 (Pb-Free)	3000/Tape & Reel
SZMMSZxxxT1G	SOD-123 (Pb-Free)	3000/Tape & Reel
MMSZxxxT3	SOD-123 (Pb-Free)	10,000/Tape & Reel
SZMMSZxxxT3G	SOD-123 (Pb-Free)	10,000/Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


DEVICE MARKING INFORMATION

See specific marking information in the device marking column of the Electrical Characteristics table on page 3 of this data sheet.

MMSZxxxT1 Series, SZMMSZxxxT1G Series

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted, $V_F = 0.95\text{ V Max. @ } I_F = 10\text{ mA}$)

Symbol	Parameter
V_Z	Reverse Zener Voltage @ I_{ZT}
I_{ZT}	Reverse Current
Z_{ZT}	Maximum Zener Impedance @ I_{ZT}
I_R	Reverse Leakage Current @ V_R
V_R	Reverse Voltage
I_F	Forward Current
V_F	Forward Voltage @ I_F



MMSZxxxT1 Series, SZMMSZxxxT1G Series

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted, $V_F = 0.9\text{ V Max.}$ @ $I_F = 10\text{ mA}$)

Device†	Device Marking	V _{Z1} (Volts) (Notes 3 and 4)			Z _{ZT1} (Note 5)	V _{Z2} (Volts) (Notes 3 and 4)		Z _{ZT2} (Note 5)	Max Reverse Leakage Current	
		@ I _{ZT1} = 5 mA				@ I _{ZT2} = 1 mA			I _R @ V _R	
		Min	Nom	Max	Ω	Min	Max	Ω	μA	Volts
SZ/MMSZ2V4T1	T1	2.28	2.4	2.52	100	1.7	2.1	600	50	1
SZ/MMSZ2V7T1	T2	2.57	2.7	2.84	100	1.9	2.4	600	20	1
MMSZ3V0T1*	T3	2.85	3.0	3.15	95	2.1	2.7	600	10	1
SZ/MMSZ3V3T1	T4	3.14	3.3	3.47	95	2.3	2.9	600	5	1
SZ/MMSZ3V6T1	T5	3.42	3.6	3.78	90	2.7	3.3	600	5	1
SZ/MMSZ3V9T1	U1	3.71	3.9	4.10	90	2.9	3.5	600	3	1
SZ/MMSZ4V3T1	U2	4.09	4.3	4.52	90	3.3	4.0	600	3	1
SZ/MMSZ4V7T1	U3	4.47	4.7	4.94	80	3.7	4.7	500	3	2
SZ/MMSZ5V1T1	U4	4.85	5.1	5.36	60	4.2	5.3	480	2	2
SZ/MMSZ5V6T1*	U5	5.32	5.6	5.88	40	4.8	6.0	400	1	2
SZ/MMSZ6V2T1*	V1	5.89	6.2	6.51	10	5.6	6.6	150	3	4
SZ/MMSZ6V8T1	V2	6.46	6.8	7.14	15	6.3	7.2	80	2	4
SZ/MMSZ7V5T1	V3	7.13	7.5	7.88	15	6.9	7.9	80	1	5
SZ/MMSZ8V2T1	V4	7.79	8.2	8.61	15	7.6	8.7	80	0.7	5
SZ/MMSZ9V1T1	V5	8.65	9.1	9.56	15	8.4	9.6	100	0.5	6
SZ/MMSZ10T1	A1	9.50	10	10.50	20	9.3	10.6	150	0.2	7
SZ/MMSZ11T1	A2	10.45	11	11.55	20	10.2	11.6	150	0.1	8
SZ/MMSZ12T1	A3	11.40	12	12.60	25	11.2	12.7	150	0.1	8
SZ/MMSZ13T1	A4	12.35	13	13.65	30	12.3	14.0	170	0.1	8
SZ/MMSZ15T1	A5	14.25	15	15.75	30	13.7	15.5	200	0.05	10.5
SZ/MMSZ16T1	X1	15.20	16	16.80	40	15.2	17.0	200	0.05	11.2
SZ/MMSZ18T1	X2	17.10	18	18.90	45	16.7	19.0	225	0.05	12.6
SZ/MMSZ20T1	X3	19.00	20	21.00	55	18.7	21.1	225	0.05	14
SZ/MMSZ22T1	X4	20.90	22	23.10	55	20.7	23.2	250	0.05	15.4
SZ/MMSZ24T1	X5	22.80	24	25.20	70	22.7	25.5	250	0.05	16.8

3. The type numbers shown have a standard tolerance of $\pm 5\%$ on the nominal Zener Voltage.

4. Tolerance and Voltage Designation: Zener Voltage (V_Z) is measured with the Zener Current applied for $PW = 1\text{ ms}$.

5. Z_{ZT} and Z_{ZK} are measured by dividing the AC voltage drop across the device by the AC current applied.

The specified limits are for $I_{Z(AC)} = 0.1 I_{Z(DC)}$ with the AC frequency = 1 kHz.

†The "G" suffix indicates Pb-Free package available.

*Not Available in the 10,000/Tape & Reel.

MMSZxxxT1 Series, SZMMSZxxxT1G Series

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted, $V_F = 0.9\text{ V Max.}$ @ $I_F = 10\text{ mA}$)

Device [†]	Device Marking	V _{Z1} (Volts) (Notes 6 and 7)			Z _{ZT1} (Note 8)	V _{Z2} (Volts) (Notes 6 and 7)		Z _{ZT2} (Note 8)	Max Reverse Leakage Current	
		@ I _{ZT1} = 2 mA				@ I _{ZT2} = 0.1 mA		@ I _{ZT2} = 0.5 mA	I _R @ V _R	
		Min	Nom	Max	Ω	Min	Max	Ω	μA	Volts
SZ/MMSZ27T1/T3	Y1	25.65	27	28.35	80	25	28.9	300	0.05	18.9
SZ/MMSZ30T1*	Y2	28.50	30	31.50	80	27.8	32	300	0.05	21
SZ/MMSZ33T1	Y3	31.35	33	34.65	80	30.8	35	325	0.05	23.1
SZ/MMSZ36T1*	Y4	34.20	36	37.80	90	33.8	38	350	0.05	25.2
SZ/MMSZ39T1*	Y5	37.05	39	40.95	130	36.7	41	350	0.05	27.3
MMSZ43T1*	Z1	40.85	43	45.15	150	39.7	46	375	0.05	30.1
MMSZ47T1	Z2	44.65	47	49.35	170	43.7	50	375	0.05	32.9
MMSZ51T1*	Z3	48.45	51	53.55	180	47.6	54	400	0.05	35.7
MMSZ56T1	Z4	53.20	56	58.80	200	51.5	60	425	0.05	39.2

6. The type numbers shown have a standard tolerance of $\pm 5\%$ on the nominal Zener Voltage.

7. Tolerance and Voltage Designation: Zener Voltage (V_Z) is measured with the Zener Current applied for $PW = 1\text{ ms}$.

8. Z_{ZT} and Z_{ZK} are measured by dividing the AC voltage drop across the device by the AC current applied.

The specified limits are for $I_{Z(AC)} = 0.1 I_{Z(DC)}$ with the AC frequency = 1 kHz.

[†]The "G" suffix indicates Pb-Free package available.

*Not Available in the 10,000/Tape & Reel.

MMSZxxxT1 Series, SZMMSZxxxT1G Series

TYPICAL CHARACTERISTICS




Figure 1. Temperature Coefficients
(Temperature Range -55°C to +150°C)




Figure 2. Temperature Coefficients
(Temperature Range -55°C to +150°C)




Figure 3. Steady State Power Derating




Figure 4. Maximum Nonrepetitive Surge Power




Figure 5. Effect of Zener Voltage on
Zener Impedance




Figure 6. Typical Forward Voltage

MMSZxxxT1 Series, SZMMSZxxxT1G Series

TYPICAL CHARACTERISTICS




Figure 7. Typical Capacitance




Figure 8. Typical Leakage Current




Figure 9. Zener Voltage versus Zener Current (V_Z Up to 12 V)






Figure 10. Zener Voltage versus Zener Current (12 V to 91 V)

MMSZxxxT1 Series, SZMMSZxxxT1G Series

PACKAGE DIMENSIONS

SOD-123
CASE 425-04
ISSUE G




- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.

DIM	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.94	1.17	1.35	0.037	0.046	0.053
A1	0.00	0.05	0.10	0.000	0.002	0.004
b	0.51	0.61	0.71	0.020	0.024	0.028
c	---	---	0.15	---	---	0.006
D	1.40	1.60	1.80	0.055	0.063	0.071
E	2.54	2.69	2.84	0.100	0.106	0.112
H_E	3.56	3.68	3.86	0.140	0.145	0.152
L	0.25	---	---	0.010	---	---
θ	0°	---	10°	0°	---	10°

STYLE 1:
PIN 1: CATHODE
2: ANODE

SOLDERING FOOTPRINT*



SCALE 10:1 (mm/inches)

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative

MMSZ2V4T1/D