



**Part Number :** [1205030011](#)

**Product Description :** Micro-Change (M12) Field Attachable Connector, 5 Poles, L-Coded, Angled, Female, Unshielded, Screw Termination, Cable Diameter 8.00-13.00mm

**Series Number :** 120503

**Status :** Active

**Product Category :** Circular Industrial Connectors

**Engineering Part Number :** LAP5001-44



---

## Documents and Resources


### Drawings

[1205030011\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Circular Industrial Connectors
Series	120503
Description	Micro-Change (M12) Field Attachable Connector, 5 Poles, L-Coded, Angled, Female, Unshielded, Screw Termination, Cable Diameter 8.00-13.00mm
Approvals	UKCA, CE certified
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Field Attachable Connector
UPC	193264730209

### Electrical

Current - Maximum per Contact	12.0A, 16.0A
Voltage - Maximum	63V

### Physical

Cable Diameter	8.00-13.00mm (.315-.512")
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	L-Coded
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	Aluminum Die-Cast

Material - Plating Mating	Gold
Orientation	Angled
Poles	5
Temperature Range - Operating	-40° to +85°C
Wire Size (AWG)	14, 16

---

This document was generated on Jun 12, 2026