





REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	LOOSE PIECE RELEASE	08/22/24	CJF	-
A2	-	ZONE B LENGTH AND ADDED NOTE 9	11/07/25	CJF	-



SECTION A-A

SECTION B-B

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL: COPPER ALLOY
2. PLATING: SEE PART NUMBER CHART
FOR GOLD PLATED CONTACTS: SELECTIVE
GOLD FLASH IN CONTACT ZONE ONLY.
3. CONTACT SIZE: 16
4. SPECIFICATIONS:
 - 4.1 CURRENT RATING: 13 AMPS
 - 4.2 CONTACT MILLIVOLT DROP: 100 MILLIVOLT
DROP @ 13 AMP TEST CURRENT.
 - 4.3 RoHS COMPLIANT
5. RECOMMENDED WIRE RANGE: 14 - 16 AWG
6. PACKAGE: 50 PCS PER BAG.
7. AVAILABLE HAND TOOL: ATT-16-00
8. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY

PART NUMBER CHART	
<u>PLATING</u>	<u>PART NUMBERS</u>
NICKEL	AT62-14-0122-LP
GOLD	AT62-14-0144-LP

SEE PART NUMBER CHART		DESCRIPTION		ITEM
PART NUMBER				
QUANTITY	MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED: 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC +0.30 2 PL DEC +0.15 3 PL DEC +0.08 3) Note reference =  MATERIAL SPECIFICATIONS: PROCESS SPECIFICATIONS: NEXT ASSY:	SIGNATURES	DATE	 Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036 CONTACT, SOCKET, STAMPED, 50PCS PER BAG, SIZE 16, 14-16 AWG, AT & AHD-9 SERIES B C- SIZE TYPE DWG NO: AT62-14-01XX-LP REVISION A2	
	DRAWN: D PARKS	10/21/13		
	CHECKED:			
	ENGINEER:			
	APPROVAL:			
CUSTOMER:			B C- SIZE TYPE DWG NO: AT62-14-01XX-LP REVISION A2	
THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.				
NEXT ASSY:	SCALE	NONE	SHEET	1 OF 1