




NOTES:

1. Electrical rating 250 Volts, 1000 Watts.
2. Use with G4, GX5.3 or G635 style lamps.
3. Contact retention force 2.0 - 4.0 lbs. per contact.



DIMENSIONS ARE IN mm (INCHES)

TOLERANCE UNLESS OTHERWISE SPECIFIED

1 PL +/- REF.

2 PL +/- REF.

ANGLE +/-

JKL COMPONENTS CORPORATION

TITLE

MR16 LAMP SOCKET

REV. NO. A

ADD NOTES RELEASED

2/11/13

11/26/07

DRAWN BY L. WENGSTROM

APP'D BY L.R.

DATE 2/11/13

SIZE A

FSCM NO. 55335

DRAWING NO. 2993-G6

- CAD DRAWING -

MANUAL REVISIONS NOT PERMITTED

SCALE NONE

RELEASED DATE 11/26/07

REVISION DATE 2/11/13

REV. NO. A

SHEET 1 OF 1