Part Number : 2137160001
Product Description : Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Right-Angle, Top Mount, Dual Row, Through Hole, Gold (Au) Flash over Palladium Nickel Plating
Series Number : 213716
Status : Active
Product Category : I/O Connectors



Documents and Resources

Drawings

2137160001_sd.pdf

2137169999-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2137160001-000.pdf

2137160001-100.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	213716
Description	Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Right-Angle, Top Mount, Dual Row, Through Hole, Gold (Au) Flash over Palladium Nickel Plating
Application	Wire-to-Board
Component Type	Receptacle
Product Name	USB
Standard	USB 2.0
Type	C
UPC	193264275694

Electrical

Current - Maximum per Contact	5.0A
Grounding to Panel	None
Shielded	Yes
Shield Type	Full Shield
Voltage - Maximum	30V AC/DC

Downloaded from Arrow.com.

Physical

Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Female
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Palladium Nickel
Material - Resin	High Temperature Thermoplastic
Mounting Style	Top-Mount
Net Weight	0.583/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	0.80mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.762µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-30° to +85°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No

Mates With / Use With

Mates with Part(s)

Description	Part Number
Universal Serial Bus (USB) Shielded I/O Plug, Type C, Right-	1054440001

Downloaded from Arrow.com.

Angle, Surface Mount, 0.76µm Gold (Au) Plating, Tray	
Universal Serial Bus (USB) Shielded I/O Plug, Type C, Right-Angle, Surface Mount, 0.76µm Gold (Au) Plating, Tape and Reel	1054440011

Downloaded from Arrow.com.