
SMD / SMT Inductors (Coils)

MLF1608A4R7KTD25

Product Status	Production
Applications	Automotive Grade
Feature	AEC-Q200AEC-Q200 No DirectivityNo Directivity MultilayerMultilayer ShieldMagnetic Shield Ferrite CoreFerrite Core
Series | Type	MLF
Brand	TDK
Environmental Compliance	RoHS, REACH, Halogen Free, Lead Free



Size	
Length(L)	1.60mm ±0.15mm
Width(W)	0.80mm ±0.15mm
Thickness | Height	0.80mm ±0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.

Electrical Characteristics	
Inductance	4.7µH ±10% at 10MHz
Rated Current (L Change) [Typ.]	
Rated Current (L Change) [Max.]	30mA
Rated Current (Temperature Rise) [Typ.]	
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	750mΩ
DC Resistance [Max.]	1.6Ω
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	55MHz
Self Resonant Frequency [Typ.]	80MHz
Q [Min.]	35 at 10MHz
Q [Typ.]	60 at 10MHz

Other	
Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow Iron Soldering
AEC-Q200	YES

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.

SMD / SMT Inductors (Coils)

MLF1608A4R7KTD25


Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000pcs
Weight	0.004g
FIT (Failure In Time)	Please contact us

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.


Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)

Impedance




MLF1608A4R7KTD25

Rac




MLF1608A4R7KTD25

Inductance



MLF1608A4R7KTD25

Q



MLF1608A4R7KTD25

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.


Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.

SMD / SMT Inductors (Coils)

MLF1608A4R7KTD25


Associated Images

Shapes and Dimensions



Dimensions in mm

Land Pattern (Terminal Connection)



Dimensions in mm

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Copyright(c) TDK Corporation. All rights reserved.
Downloaded from Arrow.com.