



Features

- Designed for 100Vac line
- Compact shape for general purpose use



Applications

- Suppressing noise occurring in automatic machines, office appliances and power source

• Model numbering system


Series Name	Resistance	Capacitance
S Bare wire	1 2 0	033 0.033μF
SB Flex PVC wire		1 0.1μF
		2 0.2μF
		3 0.3μF
		5 0.5μF

• Circuit




• Dimensions

S series (Bare wire)



SB series (Flex PVC wire)



Unit: mm

Electrical Specifications

Rated Voltage **150Vac**

Model number	Capacitance μF±20%	Resistance Ω±30%	Dimensions (mm)						Pulse condition (max.)				Peak pulse voltage	Test voltage	Insulation resistance		
			W	H	T	F	d	L	Peak to peak	Pulse width	Repetitive frequency	Pulse width (sec) x Frequency(Hz)					
S120033	0.033	120(1/4W)	16.0	16.0	7.0	14.5	0.6±0.05	20.0	650V max.	120Hz. max.	20msec.max.	3max.	700V	Line to Line 750Vdc or 375Vac 50/60Hz 60sec	Line to Line 10,000MΩ min. Line to Case 100,000MΩ min. (S series: at 500Vdc SB series: at 100dc)		
S1201	0.1																
S1202	0.2	120(1/2W)	18.0	22.0	11.0	15.5	0.8±0.07	15.0								50msec.max.	1max.
S1203	0.3																
S1205	0.5		23.0	22.5	11.5	20.0										0.5max.	
SB120033	0.033	120(1/4W)	16.0	18.0	8.0	12.5	-	-								20msec.max.	3max.
SB1201	0.1		16.0	18.0	8.0	12.5											
SB1202	0.2		19.0	25.0	8.5	15.0											
SB1203	0.3		21.5	28.0	11.0	17.0											

*Peak to peak value of pulse condition (max.) is the maximum pulse voltage that is overlapped to line voltage and can apply between terminals of spark quencher.

Operating Temperature: -40~+85°C