

Label sheet, DIN A4 - BMKL 25X12 WH



5032374

<https://www.phoenixcontact.com/us/products/5032374>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Label sheet, DIN A4, Sheet, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, lettering field size: 25 x 12 mm, Number of individual labels: 147



Your advantages

- These labels have been specially developed for laser printers
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- Can be printed on all commercially available laser printers
- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking"
- The unperforated SK-U... sheets are available for custom label designs

Commercial Data

Item number	5032374
Packing unit	1 pc
Minimum order quantity	10 pc
Sales Key	B12
Product Key	BG2414
Catalog Page	Page 344 (C-3-2019)
GTIN	4017918095772
Weight per Piece (including packing)	15.16 g
Weight per Piece (excluding packing)	0.14 g
Customs tariff number	39199080
Country of origin	DE

Technical Data

Product properties

Product type	Device marking
--------------	----------------

Marking

Number of individual labels	147
Number of individual labels per row	7

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
---------------------------------	------------------

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Color	white
Material	Polyester
Base element material	Polyester
Components	Silicone-free
Silicone-free	yes

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

	VDMA 24364:2018-05
Result	Test passed

Scratch test for the determining scratch resistance

Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Result	Test passed
--------	-------------

UV resistance

Specification	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	Following ANSI/UL 969-2018:03
Test duration	240 h
Rating 200 °C (230 °C)	Test passed
Test duration	168 h

Testing in a condensation changing climate in the presence of sulfur dioxide

Label sheet, DIN A4 - BMKL 25X12 WH



5032374

<https://www.phoenixcontact.com/us/products/5032374>

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2


Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
Recommended ambient temperature (storage/transport)	20 °C ... 25 °C
Recommended humidity (storage/transport)	40 % ... 50 %

Dimensions

Dimensional drawing	
Width	25 mm
Length	12 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Notes

General	Print image may vary depending on laser printer
---------	---

Label sheet, DIN A4 - BMKL 25X12 WH


5032374

<https://www.phoenixcontact.com/us/products/5032374>



Drawings

Dimensional drawing



Label sheet, DIN A4 - BMKL 25X12 WH



5032374

<https://www.phoenixcontact.com/us/products/5032374>

Classifications

ECLASS

ECLASS-9.0	27400629
ECLASS-11.0	27281103
ECLASS-10.0.1	27400629

ETIM

ETIM 8.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

Label sheet, DIN A4 - BMKL 25X12 WH

5032374

<https://www.phoenixcontact.com/us/products/5032374>



Accessories

Accessories

Accessories - CMS-P1-PAD - 5144819

<https://www.phoenixcontact.com/us/products/5144819>



Accessories

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com