

## KPA8C, Pressure Bar Style Copper Lug, 1-Hole

By Burndy  
Catalog # [KPA8C](#)

Cu Mechanical Terminal, 1-Hole, #10 Stud, #14 Sol-8 AWG Str, Tin Plated



### Features

- High copper alloy terminal (tin-plated) for joining a wide range of cable to equipment pads or terminal blocks
- Tongue and body are 1-piece design, pressure bar equalizes pressure over the conductor and prevents the screw from cutting into the cable

### Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Terminal Blocks

### Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

### Conductor

Conductor - Copper Str Size	<ul style="list-style-type: none"> <li>• 14 AWG</li> <li>• 12 AWG</li> <li>• 10 AWG</li> <li>• 9 AWG</li> <li>• 8 AWG</li> </ul>
Conductor Size	14-8 AWG
Conductor - Copper Str Navy Size Range	4 (1) Navy-14 (140) Navy
Conductor - Copper Str Navy Size	<ul style="list-style-type: none"> <li>• 4 (1) Navy</li> <li>• 4 (7) Navy</li> <li>• 4 (19) Navy</li> <li>• 4 (41) Navy</li> <li>• 6 (7) Navy</li> <li>• 6 (19) Navy</li> <li>• 9 (7) Navy</li> <li>• 9 (37) Navy</li> </ul>

Conductor - Copper Solid Size	<ul style="list-style-type: none"> <li>• 14 (7) Navy</li> <li>• 14 (140) Navy</li> <li>• 14 AWG</li> <li>• 13 AWG</li> <li>• 12 AWG</li> <li>• 11 AWG</li> <li>• 10 AWG</li> <li>• 9 AWG</li> <li>• 8 AWG</li> </ul>
Conductor - Copper Solid Size Range	14 AWG-8 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>
Conductor - Copper Str Size Range	14 AWG-8 AWG

### Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Pressure Bar

### Dimensions

Dimension - Pad Width inch	0.38 in
Package Height	0.000 in
Dimension - Height mm	18.3 mm
Dimension - Height inch	0.72 in
Dimension - Height fraction	18/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Dimension - Hole Size mm	5 mm
Dimension - Hole Size inch	0.21 in
Dimension - Stud Size inch	#10
Dimension - Bolt Size fraction	#10
Dimension - Width mm	10 mm
Dimension - Width inch	0.38 in
Dimension - D inch	0.47 in
Dimension - N inch	0.22 in
Dimension - Length Overall inch	0.97 in

### Force Related

Installation Torque 25 LBS/in  
Recommended in-lb

Material Copper  
Plating Type Tin  
UPC 14 Digit GTIN 00781810353455

**General**

Trade Name SCRULUG™  
Physical Attribute - Screw Type Slot  
Plated Y  
Sub Brand SCRULUG  
UPC 781810353455  
Type Bolted Lugs & Terminals

**Logistics**

Minimum Pack Quantity 1  
Carton Quantity 100

**Product Assets**

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved  
BRDY-KPA8C-SPEC-EN | REV 5/2026