


Part Number : [460812000](#)

Product Description : EXTreme PowerMass 6.38mm Pitch, Multi Path Assembly Plug, 160 Amps (4 Blades at 40 Amps per Blade), PC Tail, Tail Length 3.07mm, Lead-Free

Series Number : 46081

Status : Active

Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

[460812000 sd.pdf](#)

[PK-46081-100-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[PS-75431-999-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	46081
Description	EXTreme PowerMass 6.38mm Pitch, Multi Path Assembly Plug, 160 Amps (4 Blades at 40 Amps per Blade), PC Tail, Tail Length 3.07mm, Lead-Free
Application	Board-to-Board, Power
Comments	Multi Path (Dual 80A) Signal
Component Type	PCB Header, Plug
Product Name	EXTreme PowerMass
UPC	822350316279

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	160.0A
Voltage - Maximum	600V

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	42.493/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	2.40mm
PC Tail Length	3.07mm
Pitch - Mating Interface	6.38mm
Pitch - Termination Interface	3.00mm, 3.38mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Polarized to PCB	No
(p)ower-(s)ignal Configuration	4p - 0s
Shrouded	Closed Ends
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
EXTreme PowerMass Vertical PCB Receptacles	<u>46079</u>

This document was generated on Jan 01, 2026