



REVISION					
ZONE	LTR	ECN	DESCRIPTION	DATE	APPROVED
	C1		REVISED PER ECO-11-005139	28MAR11	HMR



9 THRU 37 CONFIGURATION

(SHOWN WITH WIRE TERMINATIONS FOR REFERENCE ONLY.
SOLDER POT TERMINATIONS ARE THE SAME CONFIGURATION)



51 CONFIGURATION

(SHOWN WITH SOLDER POT TERMINATIONS FOR REFERENCE ONLY.
WIRE TERMINATIONS ARE THE SAME CONFIGURATION)

NOTES: UNLESS OTHERWISE SPECIFIED.

- 1 MARK PER TIS.
- 2 EPOXY AS SHOWN USE 194-8102-6215/6225.
- 3 EPOXY WICKING: UNINSULATED WIRE: .050 MAX
INSULATED WIRE UPTO #25 AWG: .125 MAX
INSULATED WIRE UPTO #24 AWG OR LARGER: .200 MAX
- 4. CRIMP LEADS INTO CONTACTS PER MEP302-05.
- 5 NO SCRATCHES SHOWING BASE METAL PERMITTED ON SOLDER POTS.
- 6 CHAMFER ON SOLDER POTS ARE TO BE PARALLEL WITH SIDES OF CONNECTOR WITHIN 10°.

TE CONNECTIVITY 7-1532141-2
Micro P/N 094-0000-0011

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCE ARE:		APPROVALS		 TE Connectivity		
FRACTIONS	DECIMALS	ANGLES	SIGNATURE	DATE		
± 1/8	.XX ± .01 .XXX ± .005	± 2°	DRAWN BY <i>[Signature]</i>	9/2/99		
MATERIAL:			P.E.			
			M.E.		METAL SHELL "D" CONNECTOR PLUG, PER MIL-PRF-8351 3 SIZE 9 THRU 51	
			Q.A.			
FINISH:					SIZE B	CODE 98278
					IDENT NO.	DRAWING NO. 7-1532141-2
					SCALE: NONE	SHEET 1 OF 1