


LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	EG00-2668-01	10SEP2001	SS	JE
			A1	EG00-2859-01	20SEP2001	SS	JE



GROMMET, BLACK, 0.22 - 0.35mm²
USED FOR INSULATION DIAMETER 1.2-1.4mm

T&B UNIVERSAL PART No	106099
TYCO PART No	1-1437713-1
T&B FORD PART No	-
FORD PART No	91AG-10C930-AA
TYCO PART No	 9-1437714-1

GROMMET, RED, 0.5 - 1.0mm²
USED FOR INSULATION DIAMETER 1.4 - 2.1mm

T&B UNIVERSAL PART No	106100
TYCO PART No	1-1437713-2
T&B FORD PART No	-
FORD PART No	89FG-10C930-AA
TYCO PART No	 1-1437708-5

MATERIAL: SILICON, SELFGREASING/
Werkstoff: Silikon, selbsschmierend

TENSILE STRENGTH: MIN. 6.0N/mm²/DIN 53504 S-2
Zugfestigkeit: min. 6.0 N/mm² /DIN 53504 S-2

ELONGATION: MIN. 375% /DIN 53504 S-2
Reissdehnung: min. 375% /DIN 53504 S-2

HARDNESS: 50+/-5 SHORE A /DIN 53505 MEASURED AT PROOF PLANES
Haerte: 50+/-5 Shore A /DIN 53505 gemessen an Pruefplatten

SEALING RIBS WITHOUT SINK MARKS AND NOTCHES
Dichtrippen ohne Einfallstellen und Kerben

 INJECTION POINT PERMITTED
Anspritzung zulaessig

(A1) OBSOLETE, SUPERSEDED BY 1-1437713-1

Ⓐ **2** OBSOLETE, SUPERSEDED BY 1-1437713-2

GROMMET, BLUE, 1.5mm ² USED FOR INSULATION DIAMETER 2,2 - 2,4mm

T&B UNIVERSAL PART No	106101
TYCO PART No	1-1437713-3
T&B FORD PART No	-
FORD PART No	89FG-10C930-BA
TYCO PART No	 1-1437708-7

BLIND PLUG, WHITE

T&B UNIVERSAL PART No	106102
TYCO PART No	1-1437713-4
T&B FORD PART No	-
FORD PART No	89FG-10C930-AAA
TYCO PART No	 1-1437708-8

Ⓐ **3** OBSOLETE, SUPERSEDED BY 1-1437713-3

(A1) **4** OBSOLETE, SUPERSEDED BY 1-1437713-4

1-1437713-1	0.0815g	BLACK/schwarz	GROMMET/ Dichtung 0.22-0.35mm ²	1
1-1437713-2	0.0894g	RED/rot	GROMMET/ Dichtung 0.50-1.00mm ²	2
1-1437713-3	0.0854g	BLUE/blau	GROMMET/ Dichtung 1.5mm ²	3
1-1437713-4	0.1044g	WHITE/weiss	BLIND PLUG/ Blindstopfen	4
TYCO PART NO/ TYCO Teile Nr	WEIGHT/ Gewicht	COLOUR/ Farbe	DESCRIPTION/ Beschreibung	POS/ Pos

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION		DWN 10SEP2001 S.Storch		tyco Electronics		tyco Electronics AMP GmbH D - 64625 Bensheim	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		-	
		APVD 20SEP2001 J.Evans		PRODUCT SPEC		GROMMET	
		-		-		Einzeldrahtdichtung	
		APPLICATION SPEC		-		-	
		-		-		-	
MATERIAL -		FINISH -		WEIGHT -		RESTRICTED TO	
				A2 00779 C=1418068		-	
CUSTOMER DRAWING				SCALE 5:1		SHEET 1 OF 1	
						REV A1	