




Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image







To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

General ordering data

Version	Feed-through terminal, Tension-clamp connection, 1.5 mm 2 , 500 V, 17.5 A, dark beige
Order No.	<u>1775530000</u>
Туре	ZDU 1.5/3AN
GTIN (EAN)	4032248181490
Qty.	100 ST



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals

Approvals









ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (UR)	E60693
Certificate No. (cURusEX)	E184763

Dimensions and weights

Depth	36.5 mm	Depth (inches)	1.437 inch
Depth including DIN rail	37 mm	Height	63.5 mm
Height (inches)	2.5 inch	Width	3.5 mm
Width (inches)	0.1378 inch	Net weight	5.21 g

Temperatures

Storage temperature	-25 °C55 °C	Ambient temperature	-5 °C40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Product Carbon Footprint	Cradle to gate	0.522 kg CO2 eq.

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

Rating data IECEx/ATEX

Certificate No. (ATEX)	DEMKO15ATEX1467U	Certificate No. (IECEX)	IECEXULD15.0008U
Max. voltage (ATEX)	550 V	Current (ATEX)	15 A
Wire cross section max. (ATEX)	1.5 mm²	Max. voltage (IECEX)	550 V
Wire cross section max. (IECEX)	1.5 mm ²	Marking EN 60079-7	Ex eb II C Gb
Ex 2014/34/EU label	II 2 G D		

System specifications

Version	Tension-clamp connection, for plug-in cross-connector, One end without connector	End cover plate required	Yes
Number of potentials	1	Number of levels	1
Number of clamping points per level	3	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35		

Creation date 05.07.2025 03:02:12 MEZ

2 Catalogue status / Drawings



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Δd	ditic	nal t	achn	ادعا	data
Au		niai L	eciii	L.a.	uata

Wire cross section min. (CSA)

Open sides	right	Number of similar terminals	1
Explosion-tested version	Yes	Type of mounting	Snap-on
CSA rating data	,		'
Wire cross section max. (CSA)	14 AWG	Voltage size C (CSA)	300 V
Current size C/CCA)	20.4	Cortificate No. (CCA)	200020 1152902

Conductors for clamping (additional connection)

Connection type, additional connection Tension-clamp connection

26 AWG

Conductors for clamping (rated connection)

Gauge to IEC 60947-1	B1		
Wire connection cross section AWG.	AWG 16		
max.	AVVG 10		
Connection direction	top		
Stripping length	10 mm		
Type of connection	Tension-clamp connection		
Number of connections	3		
Clamping range, max.	1.5 mm ²		
Clamping range, min.	0.05 mm ²		
Blade size	0.4 x 2.0 mm		
Wire connection cross section AWG.	AWG 28		
min.	AWG 20		
Wire connection cross-section, finely stranded with wire-end ferrules DIN	1 mm ²		
46228/4, max.			
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm ²		
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1.5 mm²		
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm ²		
Wire connection cross section, finely stranded, max.	1.5 mm ²		
Wire connection cross section, finely stranded, min.	0.5 mm ²		
Connection cross-section, stranded, max.	1.5 mm ²		
Connection cross-section, stranded, m	in. 0.5 mm²		
Twin wire-end ferrules, max.	0.75 mm ²		
Twin wire-end ferrules, min.	0.5 mm ²		
Wire connection cross-section, solid	1.5 mm ²		
core, max.			
Wire connection cross-section, solid core, min.	0.5 mm ²		
Tube length for wire-end ferrule with	Tube length	min.	6 mm
plastic collar DIN 46228/4	1450 10119111	max.	10 mm
	Cross-section for conductor connection	nominal	0.5 mm ²
	Tube length	min.	6 mm
		max.	12 mm
	Cross-section for conductor connection	nominal	0.75 mm ²

Creation date 05.07.2025 03:02:12 MEZ

Catalogue status / Drawings





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

	Tube length	min.	6 mm
		max.	12 mm
	Cross-section for conductor connection	nominal	1 mm²
Tube length for wire-end ferrule without	Tube length	nominal	10 mm
plastic collar DIN 46228/1	Cross-section for conductor connection	nominal	0.5 mm ²
	Tube length	nominal	10 mm
	Cross-section for conductor connection	nominal	0.75 mm ²
	Tube length	nominal	10 mm
	Cross-section for conductor connection	nominal	1 mm²
	Tube length	min.	10 mm
		max.	12 mm
	Cross-section for conductor connection	nominal	1.5 mm ²

General

Wire connection cross section AWG,	AWG 16	Wire connection cross section AWG,	AWG 28
max.		min.	
Standards	IEC 60947-7-1	Rail	TS 35

Rating data

Rated cross-section	1.5 mm ²	Rated voltage	500 V
Rated DC voltage	500 V	Rated current	17.5 A
Current at maximum wires	17.5 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	1.83 mΩ	Rated impulse withstand voltage	6 kV
Power loss in accordance with IEC 60947-7-x	0.56 W	Pollution severity	3

UL rating data

Conductor size Factory wiring max. (UF	R) 14 AWG	Current size C (UR)	15 A
Voltage size C (UR)	300 V	Conductor size Factory wiring min. (UR)	26 AWG
Certificate No. (UR)	E60693	Conductor size Field wiring min. (UR)	26 AWG
Conductor size Field wiring max. (UR)	14 AWG		

Classifications

ETIM 6.0	EC000897	ETIM 7.0	EC000897
ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 9.0	27-14-11-20
ECLASS 9.1	27-14-11-20	ECLASS 10.0	27-14-11-20
ECLASS 11.0	27-14-11-20	ECLASS 12.0	27-14-11-20
ECLASS 13.0	27-25-01-01	ECLASS 14.0	27-25-01-01
ECLASS 15.0	27-25-01-01		

Data sheet

ZDU 1.5/3AN



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

1.5 mm²

1.5

 mm^2

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

General ordering data

Туре	ZQV 1.5/2	Version
Order No.	<u>1776120000</u>	Accessories, Cross-connector, 17.5 A
GTIN (EAN)	4032248200139	
Qty.	60 ST	
Туре	ZQV 1.5/3	Version
Order No.	<u>1776130000</u>	Accessories, Cross-connector, 17.5 A
GTIN (EAN)	4032248200153	
Qty.	60 ST	
Туре	ZQV 1.5/4	Version
Order No.	<u>1776140000</u>	Accessories, Cross-connector, 17.5 A
GTIN (EAN)	4032248200160	
Qty.	60 ST	
Туре	ZQV 1.5/5	Version
Order No.	<u>1776150000</u>	Accessories, Cross-connector, 17.5 A
GTIN (EAN)	4032248236336	
Qty.	20 ST	
Type	ZQV 1.5/10	Version
Type Order No.	ZQV 1.5/10 1776200000	Version Accessories, Cross-connector, 17.5 A
Order No.	1776200000	
Order No. GTIN (EAN)	<u>1776200000</u> 4032248200177	
Order No. GTIN (EAN) Oty.	1776200000 4032248200177 20 ST	Accessories, Cross-connector, 17.5 A
Order No. GTIN (EAN) Qty. Type	1776200000 4032248200177 20 ST ZAP/TW ZDU1.5/3AN	Accessories, Cross-connector, 17.5 A Version
Order No. GTIN (EAN) Qty. Type Order No.	1776200000 4032248200177 20 ST ZAP/TW ZDU1.5/3AN 1776060000	Accessories, Cross-connector, 17.5 A Version
Order No. GTIN (EAN) Oty. Type Order No. GTIN (EAN)	1776200000 4032248200177 20 ST ZAP/TW ZDU1.5/3AN 1776060000 4032248188147	Accessories, Cross-connector, 17.5 A Version
Order No. GTIN (EAN) Oty. Type Order No. GTIN (EAN) Oty.	1776200000 4032248200177 20 ST ZAP/TW ZDU1.5/3AN 1776060000 4032248188147 20 ST	Accessories, Cross-connector, 17.5 A Version Z-series, End plate, Partition plate
Order No. GTIN (EAN) Oty. Type Order No. GTIN (EAN) Oty. Type	1776200000 4032248200177 20 ST ZAP/TW ZDU1.5/3AN 1776060000 4032248188147 20 ST ZAP/TW ZDU1.5/3AN BL	Accessories, Cross-connector, 17.5 A Version Z-series, End plate, Partition plate Version
Order No. GTIN (EAN) Oty. Type Order No. GTIN (EAN) Oty. Type Order No.	1776200000 4032248200177 20 ST ZAP/TW ZDU1.5/3AN 1776060000 4032248188147 20 ST ZAP/TW ZDU1.5/3AN BL 1776070000	Accessories, Cross-connector, 17.5 A Version Z-series, End plate, Partition plate Version
Order No. GTIN (EAN) Qty. Type Order No. GTIN (EAN) Qty. Type Order No. GTIN (EAN)	1776200000 4032248200177 20 ST ZAP/TW ZDU1.5/3AN 1776060000 4032248188147 20 ST ZAP/TW ZDU1.5/3AN BL 1776070000 4032248188154	Accessories, Cross-connector, 17.5 A Version Z-series, End plate, Partition plate Version
Order No. GTIN (EAN) Qty. Type Order No. GTIN (EAN) Qty. Type Order No. GTIN (EAN) Qty. Type Order No. GTIN (EAN)	1776200000 4032248200177 20 ST ZAP/TW ZDU1.5/3AN 1776060000 4032248188147 20 ST ZAP/TW ZDU1.5/3AN BL 1776070000 4032248188154 20 ST	Version Z-series, End plate, Partition plate Version Z-series, End plate, Partition plate
Order No. GTIN (EAN) Qty. Type Order No. GTIN (EAN) Qty. Type Order No. GTIN (EAN) Qty. Type Order No. GTIN (EAN)	1776200000 4032248200177 20 ST ZAP/TW ZDU1.5/3AN 1776060000 4032248188147 20 ST ZAP/TW ZDU1.5/3AN BL 1776070000 4032248188154 20 ST ZAP/TW ZDU1.5/3AN OR	Version Z-series, End plate, Partition plate Version Z-series, End plate, Partition plate Version Version



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

SAK-Series

SAK Series

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Туре	EW 35	Version
Order No.	0383560000	End bracket, beige, TS 35, V-2, Wemid, Width: 8.5 mm, 100 °C
GTIN (EAN)	4008190181314	
Qty.	50 ST	
Туре	EW 35 GR 7032	Version
Order No.	0383530000	End bracket, grey, TS 35, V-0, Wemid, Width: 9 mm, 120 °C
GTIN (EAN)	4008190027322	
Qty.	50 ST	
Туре	EW 35/SCHA/M3	Version
Order No.	0258660000	End bracket, beige, TS 35, V-2, Wemid, Width: 16.5 mm, 100 °C
GTIN (EAN)	4008190033477	
Qty.	20 ST	

W-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Туре	WEW 35/1	Version
Order No.	1059000000	End bracket, dark beige, TS 35, V-2, Wemid, Width: 12 mm, 100 °C
GTIN (EAN)	4008190172282	
Qty.	50 ST	
Туре	WEW 35/2	Version
Type Order No.	WEW 35/2 1061200000	Version End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 °C
	'	

Creation date 05.07.2025 03:02:12 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Z-Series

Z Series Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	ZEW 35	Version
Order No.	9540000000	End bracket, dark beige, TS 35, V-2, Wemid, Width: 6 mm, 100 °C
GTIN (EAN)	4008190956264	
Qty.	20 ST	
Туре	ZEW 35/2	Version
Order No.	<u>8630740000</u>	End bracket, dark beige, TS 35, V-2, Wemid, Width: 8 mm, 100 °C
GTIN (EAN)	4032248348916	
Qty.	20 ST	
Туре	ZRH 1.5S/1	Version
Order No.	<u>1781950000</u>	Accessories, Reducing sleeve
GTIN (EAN)	4032248199525	
GTIN (EAN) Oty.	4032248199525 500 ST	
		Version
Qty.	500 ST	Version Z-series, Cover
Qty.	500 ST ZAD 7/4	

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	DEK 5/3.5 MC NE WS	Version
Order No.	<u>1755270000</u>	Dekafix, Terminal marker, 5 x 3.5 mm, Pitch in mm (P): 3.50
GTIN (EAN)	4032248017348	Weidmueller, white
Qty.	500 ST	

Creation date 05.07.2025 03:02:12 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Type WS 12/3.5 MC NE WS
Order No. 1778270000
GTIN (EAN) 4032248161041
Oty. 600 ST

Version

WS, Terminal marker, 12 x 3.5 mm, Pitch in mm (P): 3.50

Weidmueller, Allen-Bradley, white

DEK 5/3.5



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- · Firm hold and durable printing
- · Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- · Large label field for optimal legibility
- · High flexibility thanks to manufacturer independence

General ordering data

Type DEK 5/3.5 MM WS
Order No. 2007 100000
GTIN (EAN) 4050 11839 1992
Oty. 1000 ST

Version

Dekafix, Terminal marker, 5 x 3.5 mm, Weidmueller, white

WS 12/3.5



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- · Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

Creation date 05.07.2025 03:02:12 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

General ordering data

Туре	WS 12/3.5 MIM WS
Order No.	2007180000
GTIN (EAN)	4050118392203
Qty.	1000 ST

Version WS, Terminal marker, 12 x 3.5 mm, Weidmueller, white

Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

General ordering data

Туре	SDS 0.4X2.0X60
Order No.	2749260000
GTIN (EAN)	4050118895537
Qty.	1 ST

Version

Screwdriver, Blade width (B): 2 mm, Blade length: 60 mm, Blade thickness (A): 0.4 mm