


SMT Power Inductors

High Current Composite Inductor - PA2247XXXNLT and PM2247.XXXNLT



 **Pulse**
a YAGEO company

- ④ **Height:** 10.0mm Max
- ④ **Footprint:** 16.8mm x 15.8mm Max
- ④ **Current Rating:** up to 30Arms
- ④ **Inductance Range:** 4.7uH to 33.0uH
- ④ High current, low DCR, and high efficiency
- ④ Rated Voltage between Terminals: 100V
- ④ Minimized acoustic noise and minimized leakage flux noise
- ④ Available in Commercial (PA2247) and Automotive (PM2247) grades

Electrical Specifications @ 25°C, Operating Temperature Range -55°C to +155°C

Part Number		④ Inductance 100KHz, 0.1V	Rated ³ Current	DC Resistance		Saturation Current ² (25°C)	K Factor for Core Loss
				TYP.	MAX.		
Commercial	Automotive ⁶	uH±20%	A	mΩ	mΩ	A	
PA2247.472NLT	PM2247.472NLT	4.7	30	3.4	3.8	39	10.9
PA2247.562NLT	PM2247.562NLT	5.6	28	3.82	4.2	34	9.6
PA2247.682NLT	PM2247.682NLT	6.8	26	4.18	4.6	31	9.6
PA2247.822NLT	PM2247.822NLT	8.2	25	6.0	7.2	28	8.6
PA2247.103NLT	PM2247.103NLT	10.0	24	7.1	8.6	26	7.2
PA2247.153NLT	PM2247.153NLT	15.0	18	9.2	11.5	20	6.1
PA2247.223NLT	PM2247.223NLT	22.0	16	13.2	15.8	18	5.0
PA2247.333NLT	PM2247.333NLT	33.0	13	18.7	20.0	16.7	3.9

Notes:

1. Actual temperature of the component during system operation (ambient plus temperature rise) must be within the standard operating range.
2. The saturation current is the current at which the initial inductance is guaranteed to drop by no more than 40%. The typical inductance at a specified current can be found on the typical performance curves.
3. The rated current is the DC current required to raise the component temperature by approximately 40 °C. Take note that the components' performance varies depending on the system condition. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.
4. The part temperature (ambient+temp rise) should not exceed the upper operating temperature range under worst case operating conditions. Circuit design, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
5. The PMxxxx.XXXNLT part numbers are AEC-Q200 and IATF16949 certified. The inductance and mechanical dimensions are 100% tested in production but do not necessarily meet a product capability index (Cpk) >1.33 and therefore may not strictly conform to PPAP.
6. Special Characteristics 




SMT Power Inductors

High Current Composite Inductor - PA2247XXXNLT and PM2247.XXXNLT

 **Pulse**
a YAGEO company

Mechanical

PA2247.XXXNLT and PM2247.XXXNLT




FINAL LAYOUT

SUGGESTED PAD LAYOUT

Series	A	B	C	D	E	F	L	G	H
PA2247/PM2247	16.5±0.3	15.5±0.3	9.7±0.3	13.2±0.5	3.2±0.2	10.4±0.3	15.0(REF)	6.0 (REF)	15.0(REF)

All Dimensions in mm.

TAPE & REEL INFO









SURFACE MOUNTING TYPE, REEL/TAPE LIST						
Series	REEL SIZE (mm)		TAPE SIZE (mm)			QTY PCS/REEL
	A	G	P ₁	W	K ₀	
PA2247/PM2247	Ø330	32.4	24	32	10.5	150

SMT Power Inductors

High Current Composite Inductor - PA2247XXXNLT and PM2247.XXXNLT





Typical Performance Curves




SMT Power Inductors

High Current Composite Inductor - PA2247XXXNLT and PM2247.XXXNLT



CORE LOSS vs FLUX DENSITY



For More Information:

Americas - prodinfo_power@pulseelectronics.com | **Europe** - power-apps-europe@pulseelectronics.com | **Asia** - power-apps-asia@pulseelectronics.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2021. Pulse Electronics, Inc. All rights reserved.



4

PulseElectronics.com

P864.D (05/21)

 **Pulse**
a YAGEO company